

Rackmount PDU with 8 Outlets and Surge Protection - 1U

Product ID: RKPW081915



This 8-outlet (120V 15A)(12A UL) Rack PDU delivers a cost-effective power distribution solution for your server rack/cabinet. The 1U PDU can be mounted horizontally in any server rack 4in in depth or greater, to provide eight 120V 15A power ports/outlets, and features a rugged steel casing to ensure maximum durability.

The front of the PDU features two LEDs to indicate proper ground and surge detection while enabling you to control the power state with an illuminated power/reset switch.

To prevent costly breakdowns of connected devices, the rackmount PDU features a built-in circuit breaker and reset switch, ensuring dependable performance of vital equipment.

Certifications, Reports and Compatibility

Applications

- 8 easily accessible power outlets in a compact 1U of rack space
- Localize the power control for all of your connected system

Features

- Solid Steel Chassis for durability
- Integrated 6ft power cord
- LED indicators for ground and surge detection
- Illuminated reset and power switch

- Meets ANSI/EIA RS-310-D standards
- Built in circuit breaker

Hardware

Warranty	2 Years
Form Factor	Horizontal
Number of Power Outlets	8
Rack-Mountable	Yes

Performance

General Specifications	Surge Protection: 1800 Joules
Maximum Total Current	15A
Maximum Total Current Draw per Phase	15A
Regulatory Derated Input Current (North America)	12A
Nominal Input Voltage	120V
Nominal Output Voltage	120V
Maximum Output Voltage	125V
Load Capacity	1800 VA

Connector(s)

Input Connector(s)	NEMA 5-15 Power (North America)
Output Connectors	NEMA 5-15 Power (North America)

Indicators

LED Indicators	Ground
	Surge

Power

Input Voltage	120 AC
---------------	--------

Environmental



Operating Temperature	-5C to 45C (23F to 113F)
Storage Temperature	-25C to 65C (-13F to 149F)
Humidity	0% RH

Physical Characteristics

Color	Black
Material	Steel
Cable Length	6.0 ft [1.8 m]
Product Length	19.0 in [48.3 cm]
Product Width	3.8 in [95.5 mm]
Product Height	1.7 in [42.7 mm]
Weight of Product	4.2 lb [1.9 kg]

Packaging Information

Package Length	18.3 in [46.5 cm]
Package Width	2.3 in [59.0 mm]
Package Height	8.9 in [22.7 cm]
Shipping (Package) Weight	4.8 lb [2.2 kg]

What's in the Box

Included in Package	8 Port Power Distribution Unit
	Installation Document

**Product appearance and specifications are subject to change without notice.*

