

DisplayPort to DVI Dual-Link Active Adapter Video Converter (M/F), 6-in. (15.24 cm)

MODEL NUMBER: P134-06N-DVI-DL







Converts any DisplayPort video signal for display on a DVI-I single-link or dual-link monitor, projector or television.

Features

Send High-Definition DisplayPort Video Signals to a DVI DisplayConnects DisplayPort computer to DVI-I dual-link monitor, projector or TVActive converter works with all DisplayPort signalsIdeal for displaying video on large monitor or digital signFemale DVI dual-link and male DisplayPort connectors Vibrant, Superior Video QualitySupports DVI dual-link video resolutions up to 2560 x 1600Supports DVI single-link video resolutions up to 1920 x 1080 (1080p)Supports 24-bit Deep Color (8 bits per channel)Converts Multi-Mode (DP++) and Single-Mode DisplayPort outputWorks with graphics cards that don't output DP++ signals, such as AMD Eyefinity

Superior Materials for Superior PerformanceGold-plated connectors and contacts for excellent conductivityIntegral strain relief for long lifePlug-and-play—no software, drivers or power supply necessaryFits easily into briefcase, backpack or laptop bag

Highlights

- Active converter works with all DisplayPort signals
- Supports DVI dual-link video resolutions up to 2560 x 1600
- Supports DVI single-link video resolutions up to 1920 x 1080
- Converts Multi-Mode (DP++) and Single-Mode DisplayPort output
- Plug and play—no software, drivers or power supply needed

System Requirements

- Computer with DisplayPort and USB port
- Display with DVI output
- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P134-06N-DVI-V2

Package Includes

 P134-06N-DVI-DL DisplayPort to DVI Dual-Link Active Converter (M/F), 6 in.

Specifications

OVERVIEW	
UPC Code	037332198716
Technology	DVI; DisplayPort
PHYSICAL	
Color	Silver
Cable Length (ft.)	0.5
Cable Length (in.)	6



	1	
Cable Length (cm)	15.24	
Shipping Dimensions (hwd / cm)	3.30 x 8.89 x 15.75	
Shipping Dimensions (hwd / in.)	1.30 x 3.50 x 6.20	
Shipping Weight (kg)	0.16	
Shipping Weight (lbs.)	0.35	
CONNECTIONS		
Side A - Connector 1	DISPLAYPORT (MALE)	
Side A - Connector 2	USB A (MALE)	
Side B - Connector 1	DVI-I DUAL LINK (FEMALE) (WIRED TO DVI-D DUAL LINK)	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies