

Vertical Dual Monitor Stand - Ergonomic Desktop Stacked Two Monitor Stand up to 27 inch VESA Mount Displays - Free Standing Universal Monitor Mount - Height Adjustable - Silver

Product ID: ARMDUOVS



This vertical dual-monitor stand, with its sleek aluminum design, raises two displays off the surface of your desk or table, to save space while increasing your productivity. With its robust construction, the freestanding dual-monitor mount securely holds two VESA mount monitors, each up to 27", stacked vertically.

The dual-monitor mount holds two displays, one above the other. You can adjust the height of the monitors along the 28" (710 mm) pole, to work in comfort with your two-monitor setup.

The adjustable monitor stand for desks enables smooth, effortless +15/-15 degree tilt and swivel, making it easy to find the perfect viewing angle. It can also rotate a full 360 degrees, giving you the flexibility of portrait or landscape viewing.

The dual-monitor stand securely holds your monitors in place while complimenting your office decor with its black and silver aluminum design. The monitor stand supports two monitors, each up to 27" (686 mm) in size and 17.6 lb. (8 kg) in weight.

The VESA monitor stand is easy to install, featuring quick monitor attachment and removal. It also provides cable management to keep your cables neatly out of sight.

ARMDUOVS is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Stack your displays vertically, ideal for web design or coding
- Increase your comfort when working on two screens

- Enhance your productivity in office settings

Features

- **27 INCH VERTICAL DUAL MONITOR STAND:** VESA 75x75/100x100mm compatible desktop multiple monitor stand supports two vertically stacked monitors up to 27" or ultrawide up to 34" (17.6lb/8kg) per screen
- **RANGE OF MOTION:** Ergonomic monitor stand w/+/-15 tilt/swivel, 360 rotation (portrait/landscape), ball joint design for ideal viewing angles, individual adjustable height of 12.4" along the 28" pole
- **STABLE & NON-SLIP:** Aluminum free standing monitor mount w/ u-shaped base (11.8" (300mm) x 20.5" (520mm)) for max stability & flexible placement; Anti-slip rubber pads prevent scratches on desk surface
- **INCREASE PRODUCTIVITY WITH LESS SPACE:** Silver vertically stacked dual monitor stand optimizes the use of the desktop space; ideal for smaller workspaces in your home office or cubicles in the office
- **ADJUSTABLE SET UP:** Universal double monitor stand w/ cable management hooks & height adjustable clips on pole to organize cables for a tidy workspace and hold included adjustment tools

Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
# of Displays Supported	2
Orientation	Vertical
Mounting Options	Desktop Stand
VESA Hole Pattern(s)	75x75 mm 100x100 mm

Performance

Weight Capacity (Per Display)	17.7 lb [8 kg]
Minimum Display Size	13"
Maximum Display Size	27in
Display Tilt	+ 15 / - 15
Swivel / Pivot	+15 / -15

Display Rotation 360

Physical Characteristics

Color	Black & Silver
Material	Aluminum and Plastic
Product Length	20.3 in [51.5 cm]
Product Width	11.4 in [29.0 cm]
Product Height	29.7 in [75.4 cm]
Weight of Product	10.3 lb [4.6 kg]

Packaging Information

Package Length	21.9 in [55.5 cm]
Package Width	13.4 in [34.0 cm]
Package Height	6.3 in [16.0 cm]
Shipping (Package) Weight	11.8 lb [5.4 kg]

What's in the Box

Included in Package	VESA Mounts
	Lower Pole
	Upper Pole
	Pole Connector
	Base
	Cable Management Hooks
	Cable Management Hook Screws
	M4 x 14 Screws
	M5 x 14 Screws
	Washers
M4 x 30 Screws	

M5 x 30 Screws

Spacers

3 mm Hex Key with Screwdriver Tip

3 mm Hex Key

4 mm Hex Key

Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***

