

6ft (1.8m) DisplayPort to DVI Cable - 1080p Video - DisplayPort to DVI Adapter Cable - DP to DVI-D Converter Single Link - DP to DVI Monitor Cable - Latching DP Connector

**Product ID:** DP2DVI2MM6



The DP2DVI2MM6 6 ft DisplayPort to DVI Adapter Cable lets you connect a DVI Display or Projector to a DisplayPort video card/source. Providing a connection distance of 6ft, the cable features male DVI and DisplayPort connectors, allowing you to make a direct video card-to-display connection, as opposed to having to use an adapter with a separate cable.

The DP to DVI cable is a convenient, cost-effective solution for taking full advantage of your DVI display, without the expense of upgrading to a DisplayPort monitor. The cable offers high quality construction and supports high bandwidth video resolutions up to 1920x1200 or HDTV resolutions up to 1080p.

DP2DVI2MM6 is a passive adapter that requires a DP++ port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port. Backed by a StarTech.com 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Connect a DisplayPort video source directly to any DVI-D (digital) display with no additional adapters required
- Re-purpose an existing DVI display for use with a new DisplayPort-equipped computer, or as a secondary display
- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays

### Features

- DISPLAYPORT TO DVI CABLE: 6ft (1.8m) DisplayPort 1.2 (HBR2) to DVI-D single-link cable connects a DVI display, monitor or projector 1920x1200/1080p 60Hz or 4K 30Hz (HDMI clock rate); HDCP 1.4 EDID ensures

compatibility between source & display

- **COMPATIBILITY:** Passive video converter supports DP++ sources including workstations, desktops (AMD/Nvidia), laptops, small form factor computers & docking stations
- **INTEGRATED DISPLAY CABLE:** DisplayPort to DVI adapter cable has slim & flexible design w/ adapter chip built into DVI connector reducing clutter & providing a tidy install in the office, boardroom or home office
- **LATCHING DISPLAYPORT & SCREW LOCKING DVI:** Latching DP connector & gold plated DVI connector ensure solid connection; Chip built into DVI connector minimizes signal loss Supports DVI screw locking cable to prevent cable accidental disconnection
- **EASY TO USE:** With no software or drivers required, the DP to DVI cable/cord works with any OS including Windows, Ubuntu and macOS; DisplayPort male to DVI male cable

---

#### Hardware

Warranty	3 Years
Active or Passive Adapter	Passive
AV Input	DisplayPort - 1.2
AV Output	DVI-D - Single-Link
Audio	No
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride

---

#### Performance

Maximum Digital Resolutions	1920x1200 / 1080p
Audio Specifications	DVI - No Audio Support

---

#### Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	DVI-D (25 pin)

---

#### Special Notes / Requirements

Note	DP++ (DisplayPort++) port is required on video card or video source for DVI and HDMI pass-through.
------	--

---

#### Environmental

Operating Temperature	0C to 45C (32F to 113F)
-----------------------	-------------------------



Storage Temperature -10C to 80C (14F to 176F)

Humidity 10%-85%RH

---

**Physical Characteristics**

Color	Black
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.6 in [40.0 mm]
Product Height	0.6 in [15.0 mm]
Weight of Product	5.0 oz [143.0 g]

---

**Packaging Information**

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	1.2 in [31.0 mm]
Shipping (Package) Weight	5.4 oz [152.0 g]

---

**What's in the Box**

Included in Package	6 ft DisplayPort to DVI Cable - M/M
---------------------	-------------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

