

## HDMI or DVI to DisplayPort Active Converter

**Product ID:** HDMI2DP



The HDMI2DP DVI or HDMI to DisplayPort Converter converts an HDMI, DVI or Mini DVI input signal into a DisplayPort (or Mini DisplayPort) output, eliminating the cost of upgrading your source device hardware or purchasing a new display.

With support for full HD resolutions up to 1920x1200, the HDMI2DP converter is the perfect solution for connecting devices that have an HDMI, DVI single-link or mini DVI output, such as video cards (desktop or laptop), video game consoles or home theater receivers, to your DisplayPort-capable display.

To connect a DVI video source to this adapter, a DVI to HDMI adapter is required. The following StarTech.com adapters are compatible with this adapter:

3 ft HDMI to DVI-D Cable (HDDVIMM3)

6 ft HDMI to DVI-D Cable (HDMIDVIMM6)

8in HDMI to DVI-D Video Cable Adapter (HDDVIMF8IN)

HDMI to DVI-D Video Cable Adapter - M/F (HDMIDVIMF)

Mini DVI to HDMI Video Adapter for Macbooks and iMacs (MDVIHDMIMF)

The HDMI2DP is backed by a 2-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays

- Keep your existing DisplayPort monitor to be used with your HDMI or DVI device

## Features

- Supports full HD resolutions up to 1920x1200
- Stores EDID information to ensure compatibility between source and display
- Supports HDMI uncompressed 2-channel audio such as LPCM
- Allows for conversion of DVI or mini-DVI sources with additional cables (not included)
- Compatible with HDMI, DVI and Mini DVI 1.0 Input
- Supports DisplayPort/Mini DisplayPort 1.1a output

---

### Hardware

|                           |             |
|---------------------------|-------------|
| Warranty                  | 2 Years     |
| Active or Passive Adapter | Active      |
| AV Input                  | HDMI        |
| AV Output                 | DisplayPort |
| Audio                     | Yes         |

---

### Performance

|                             |                     |
|-----------------------------|---------------------|
| Maximum Digital Resolutions | 1920x1200 (50/60Hz) |
| Audio Specifications        | 5.1 Surround Sound  |

---

### Connector(s)

|             |                      |
|-------------|----------------------|
| Connector A | HDMI (19 pin)        |
| Connector B | DisplayPort (20 pin) |

---

### Indicators

|                |               |
|----------------|---------------|
| LED Indicators | Red Power LED |
|----------------|---------------|

---

### Power

|               |                     |
|---------------|---------------------|
| Power Source  | AC Adapter Included |
| Input Voltage | 100 - 240 AC        |



|                              |          |
|------------------------------|----------|
| Input Current                | 0.5A     |
| Output Voltage               | 5 DC     |
| Output Current               | 2A       |
| Center Tip Polarity          | Positive |
| Plug Type                    | N        |
| Power Consumption (In Watts) | 5        |

---

#### Environmental

|                       |                                |
|-----------------------|--------------------------------|
| Operating Temperature | 0C to 70C (32F to 158F)        |
| Storage Temperature   | -10C to 80C (14F to 176F)      |
| Humidity              | 5% to 90% RH (no condensation) |

---

#### Physical Characteristics

|                   |                |
|-------------------|----------------|
| Color             | Black          |
| Material          | Steel          |
| Product Length    | 3.2 in [82 mm] |
| Product Width     | 1.7 in [43 mm] |
| Product Height    | 0.9 in [23 mm] |
| Weight of Product | 3.8 oz [109 g] |

---


#### Packaging Information

|                           |                  |
|---------------------------|------------------|
| Package Length            | 6.1 in [15.6 cm] |
| Package Width             | 8.9 in [22.7 cm] |
| Package Height            | 2.1 in [54 mm]   |
| Shipping (Package) Weight | 13.8 oz [392 g]  |

---

#### What's in the Box

|                     |                               |
|---------------------|-------------------------------|
| Included in Package | HDMI to DisplayPort converter |
|---------------------|-------------------------------|



Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand

Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

