

2 Port USB HDMI Cable KVM Switch with Audio and Remote Switch – USB Powered

Product ID: SV211HDUA



The SV211HDUA 2-Port HDMI Cable KVM Switch with Audio and Remote Switching Control lets you control two HDMI, USB equipped PCs with a single monitor, keyboard, mouse and audio peripheral set.

To help organize your desk without sacrificing work space, this compact HDMI USB KVM features integrated cables that can be connected directly to your system, while leaving a minimal footprint. The switch features a remote push-button on a 1.5 meter (5ft) integrated cable that can be placed in an easily accessible location, as well as keyboard hot-keys, and PC or Mac compatible software for switching between systems. To eliminate the need for a bulky external power adapter and wall outlet, the HDMI KVM switch is USB-powered.

This KVM with HDMI video capability offers support for 1080p HD resolutions (up to 1920x1200) for the ability to drive a large HDMI display for applications that require high graphical output.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Great for PC test/burn-in computer control, saving the desk space required for two monitors, keyboards and mice
- Perfect for sharing computers and attached peripherals in the home or home office
- Dual system control for single user workstations increasing user productivity in the office

Features

- Supports HD resolutions (1080p - 1920x1200)

- Switch PCs via push-button, hot-keys or switching software
- Space-saving design, minimal footprint
- Integrated KVM cables and remote switch
- Switching software supports PC and Mac platforms
- USB Powered - No external power adapter required
- Independent audio/mic switching for uninterrupted audio
- Analog (3.5mm) and HDMI audio supported
- Supports hot-plugging
- Remote switch on 1.5m (5ft.) cable

Hardware

| | |
|------------------------------|---------|
| Warranty | 2 Years |
| Audio | Yes |
| KVM Ports | 2 |
| PC Interface | USB |
| PC Video Type | HDMI |
| Number of Monitors Supported | 1 |
| Rack-Mountable | No |
| Cables Included | Yes |
| Industry Standards | HDCP |
| Daisy-Chain | No |

Performance

| | |
|----------------------|--------------------------------|
| On-Screen Display | No |
| IP Control | No |
| Hot-Key Selection | Yes |
| Audio Specifications | 3.5mm and HDMI audio supported |



Port Selection Support Push Button, Hotkeys, and Software

Connector(s)

| | |
|----------------------|--|
| Console Interface(s) | HDMI (19 pin) 3.5 mm Mini-Jack (3 Position) USB Type-A (4 pin) USB 2.0 |
| Host Connectors | USB Type-A (4 pin) USB 2.0 HDMI (19 pin) 3.5 mm Mini-Jack (3 Position) |

Software

| | |
|------------------|--|
| OS Compatibility | Windows 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server 2003, 2008 R2, 2012, 2016, 2019 Mac OS 10.6 to 10.12 |
|------------------|--|

Special Notes / Requirements

| | |
|------|--|
| Note | OS Compatibility refers to KVM software only - the KVM itself can be used without software on any platform |
|------|--|

Indicators

| | |
|----------------|------------------------|
| LED Indicators | PC Selection indicator |
|----------------|------------------------|

Power

| | |
|--------------|-------------|
| Power Source | USB-Powered |
|--------------|-------------|

Environmental

| | |
|-----------------------|--------------------------|
| Operating Temperature | 0C to 40C (32F to 104F) |
| Storage Temperature | -20C to 60C (4F to 140F) |
| Humidity | 0~90% RH Non-Condensing |

Physical Characteristics

| | |
|--------------|-----------------|
| Color | Black |
| Material | Plastic |
| Cable Length | 33.5 in [85 cm] |



| | |
|-------------------|-------------------|
| Product Length | 3.5 in [88.0 mm] |
| Product Width | 2.6 in [66.0 mm] |
| Product Height | 0.9 in [23.0 mm] |
| Weight of Product | 12.4 oz [350.0 g] |

Packaging Information

| | |
|---------------------------|-------------------|
| Package Length | 9.8 in [25.0 cm] |
| Package Width | 6.3 in [16.1 cm] |
| Package Height | 2.4 in [62.0 mm] |
| Shipping (Package) Weight | 16.4 oz [464.0 g] |

What's in the Box

| | |
|---------------------|--------------------|
| Included in Package | KVM Switch |
| | Software CD |
| | Instruction Manual |

****Product appearance and specifications are subject to change without notice.***

