

DisplayPort to DVI Adapter - DisplayPort to DVI-D Adapter Video Converter 1080p - DP 1.2 to DVI Monitor/Display Cable Adapter Dongle - DP to DVI Adapter - Latching DP Connector

Product ID: DP2DVI2



The DP2DVI2 DisplayPort to DVI Video Adapter Converter lets you connect a DVI monitor to DisplayPort-enabled desktop or laptop computers.

Supporting display resolutions of up to 1920x1200 allowing you to take full advantage of single link DVI capability. DP2DVI2 is a passive adapter that requires a DP++ port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port.

StarTech.com also offers the DP2DVIS, an Active DisplayPort to DVI adapter.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays
- Keep your existing DVI monitor to be used with your new DisplayPort device
- Ideal for using your DVI monitor as a secondary display

Features

- DISPLAYPORT TO DVI ADAPTER: DisplayPort 1.2 HBR2 to DVI-D (digital only) single-link adapter connects DVI display/projector 1920x1200/1080p 60Hz; HDCP 1.4 6" (15cm) attached cable DisplayPort Certified

- **COMPATIBILITY:** Passive video converter supports DP++ source incl workstations, desktops (AMD/Nvidia), laptops, small form factor computers & docking stations
- **CONNECT A PRIMARY OR SECONDARY DISPLAY:** Connect a DVI monitor or projector, or add a second display to your workstation using the DP to DVI adapter. Tested w/ DVI cables up to 25ft. EDID & DDC pass-through ensure compatibility between source & display
- **LATCHING DISPLAYPORT & SCREW LOCKING DVI:** Latching DP connector ensures a solid host connection. Supports DVI screw locking cable to prevent cable from coming loose or accidental disconnection. Compact design
- **EASY TO USE:** With no software or drivers required, the DP to DVI adapter converter works w/ any OS. DisplayPort male to DVI female adapter dongle. Connector is DVI-I, however only a digital signal (DVI-D) passes through

Hardware

Warranty	3 Years
Active or Passive Adapter	Passive
AV Input	DisplayPort - 1.2
AV Output	DVI-I (Digital Only) - Single-Link
Audio	No

Performance

Maximum Digital Resolutions	1920x1200 / 1080p
Supported Resolutions	1920x1080 (1080p)
	1680x1050 (WSXGA+)
	1600x1200
	1600x900
	1440x900
	1400x1050 (SXGA+)
	1366x768
	1360x768
	1280x1024
	1280x960
	1280x800
	1280x768 (WXGA)
	1280x720p (720p)



1280x600
1152x864
1024x768
800x600 (SVGA)
640x480 (480p)

Wide Screen Supported Yes
Audio Specifications DVI - No Audio Support

Connector(s)

Connector A DisplayPort (20 pin)
Connector B DVI-I (29 pin)

Special Notes / Requirements

System and Cable Requirements DP++ port (DisplayPort ++)
required on video card or video source (DVI and HDMI pass-through must be supported)

Environmental

Operating Temperature 0C to 45C (32F to 113F)
Storage Temperature -10C to 80C (14F to 176F)
Humidity 10%-85%RH

Physical Characteristics

Color Black
Cable Length 6.0 in [15.2 cm]
Product Length 10.0 in [25.4 cm]
Product Width 1.7 in [42.0 mm]
Product Height 0.7 in [17.0 mm]
Weight of Product 1.5 oz [43.0 g]

Packaging Information

Package Length 8.7 in [22.0 cm]
Package Width 7.9 in [20.0 cm]



Package Height 0.7 in [19.0 mm]

Shipping (Package) Weight 1.8 oz [52.0 g]

What's in the Box

Included in Package DisplayPort to DVI Converter

****Product appearance and specifications are subject to change without notice.***

