

Mini DisplayPort to DVI Adapter - Mini DP to DVI-D Converter - 1080p Video - mDP or Thunderbolt 1/2 Mac/PC to DVI Monitor - mDP 1.2 to DVI Single-Link Adapter Dongle - White

**Product ID:** MDP2DVIW



The MDP2DVIW passive Mini DisplayPort to DVI Adapter (White) offers an easy-to-use DVI/Mini-DisplayPort link that enables you to connect a DVI computer monitor to a device with a Mini-DisplayPort output (such as a laptop video out port) or video card. The adapter is the perfect accessory for any of your MacBook or Microsoft Surface Pro devices with mDP.

The adapter supports high resolution output up to 1920x1200, offering a cost-effective solution for mirroring or extending a computer desktop onto a second display. Plus, because the adapter functions passively, it can be used with a DVI to HDMI adapter, to connect an HDMI-equipped monitor to a Mini DisplayPort output.

This versatile Mini DisplayPort to DVI adapter requires a multimode DisplayPort port (DisplayPort ++ ) connection to function, and is compatible with Intel Thunderbolt output when directly connected to a supporting DisplayPort over Thunderbolt I/O port.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade shows using DVI displays
- Keep your existing DVI monitor for use with your new Mini DisplayPort device
- Ideal for using a DVI monitor as a secondary display connected through a Mini DisplayPort output

## Features

- **MINI DISPLAYPORT TO DVI ADAPTER:** mDP 1.2 (HBR2) to DVI-I (digital only DVI-D) single-link video adapter connects a DVI display or projector supporting 1920x1200 & 1080p 60Hz video; EDID/DDC pass-through ensure compatibility between source & display White
- **HOST COMPATIBILITY:** Passive video converter supports mDP++ source including Thunderbolt 1 & 2 MacBooks, MacBook Air & Mac Mini, Microsoft Surface Pro 1-6, desktops (AMD FirePro/NVidia Quadro), laptops, mini itx computers, Intel NUC & docks
- **INCREASE PRODUCTIVITY:** Connect a DVI monitor or projector, or add a second display to your workstation using the mDP to DVI adapter dongle Compact design makes it ideal for travel 4.7" (12cm) attached cable
- **SCREW LOCKING DVI:** Mini DisplayPort to DVI display adapter supports DVI screw locking cable to prevent cable from coming loose or accidental disconnection from DVI displays/projectors Tested with DVI cables up to 25ft mDP male to DVI female connector
- **EASY TO USE:** With no software or drivers required, the Mini DP to DVI converter works with any OS including Windows, Ubuntu and macOS; Compatible with MiniDP devices like TB1/TB2 MacBooks with Mini DisplayPort

---

### Hardware

Warranty	3 Years
Active or Passive Adapter	Passive
AV Input	Mini DisplayPort - 1.2
AV Output	DVI-I (Digital Only) - Single-Link
Audio	No
Industry Standards	DisplayPort 1.1a DVI 1.1

---

### Performance

Maximum Digital Resolutions	1920x1200 / 1080p
Audio Specifications	DVI - No Audio Support
MTBF	2,205,691 hours

---

### Connector(s)

Connector A	Mini-DisplayPort (20 pin)
Connector B	DVI-I (29 pin)

---

### Environmental



Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	40~85% RH

---

**Physical Characteristics**

Color	White
Material	Plastic
Cable Length	4.7 in [12 cm]
Product Length	7.1 in [18 cm]
Product Width	1.8 in [45 mm]
Product Height	0.6 in [15 mm]
Weight of Product	1.0 oz [29 g]

---

**Packaging Information**

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.6 in [15 mm]
Shipping (Package) Weight	1.5 oz [43 g]

---

**What's in the Box**

Included in Package	Mini DisplayPort to DVI Converter
---------------------	-----------------------------------

---

*\*Product appearance and specifications are subject to change without notice.*

