

USB-C to Mini DisplayPort Adapter - 4K 60Hz - White

Product ID: CDP2MDP



This USB Type-C to Mini DisplayPort adapter lets you output mini DisplayPort (mDP) video and audio from the USB Type-C port on your laptop or other device. It works with USB 3.1 or Thunderbolt 3 Type-C devices that pass an mDP video signal, such as your MacBook Pro, Chromebook or 2018 iPad Pro.

Harness the video capabilities that are built into your computer's USB-C connection, using the adapter to deliver the astonishing quality of UHD to your 4K 60Hz display.

You can achieve an output resolution of up to 3840 x 2160p at 60Hz, perfect for high-resolution tasks such as viewing 4K video. The USB-C video adapter is backward compatible with 1080p monitors or displays, which makes it a great accessory for workspace applications.

This adapter lets you use the versatile USB Type-C port on your portable device. USB-C is a reversible connector, enabling you to plug it into your device in any direction. The Thunderbolt 3 compatible adapter provides a hassle-free connection to your Windows or Mac based Thunderbolt 3 computer.

The compact USB-C to mDP adapter is lightweight and fits perfectly in your laptop bag. Its portable design is ideal for BYOD (Bring Your Own Device) applications at the office or on the road.

The CDP2MDP is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Notes:

Your USB-C device must support DisplayPort over USB-C (DP Alt Mode) to work with this adapter

This adapter outputs a single-mode Mini DisplayPort signal and will not work with additional video adapters such as Mini DisplayPort to HDMI, Mini DisplayPort to VGA or Mini DisplayPort to DVI adapters

Certifications, Reports and Compatibility

Applications

- Connect your USB-C laptop to an mDP display at work
- Deliver presentations on any boardroom mDP display from your laptop
- Connect a secondary monitor to your USB-C laptop

Features

- Enjoy UHD video resolutions up to 4K 60Hz from your USB-C device
- Achieve a hassle-free connection with the reversible USB-C connector and Thunderbolt 3 compatibility
- Maximum portability with a lightweight and easy to transport design
- Compatible with Thunderbolt 3 and USB Type-C with DP Alt Mode

Hardware

Warranty	3 Years
Active or Passive Adapter	Passive
AV Input	USB-C
AV Output	Mini DisplayPort - 1.2
Audio	Yes
Chipset ID	NXP - PTN5100 Pericom - PI3DPX1203

Performance

Video Revision	DisplayPort 1.2
Maximum Cable Distance To Display	6.6 ft [2 m]
Maximum Digital Resolutions	4K (3840 x 2160) @ 60 Hz
Supported Resolutions	1024 x 768 1280 x 720 1920 x 1080 @ 144hz 1920 x 1200



2560 x 1440
2560 x 1600
3840 x 2160 @ 60Hz

Wide Screen Supported Yes
Audio Specifications DisplayPort - 7.1 Channel Audio

Connector(s)

Connector A USB-C (24 pin) DisplayPort Alt Mode
Mini-DisplayPort (20 pin)

Special Notes / Requirements

System and Cable Requirements Your USB-C device must support DisplayPort over USB-C (DP alt mode) to work with this adapter

This adapter outputs a single-mode Mini DisplayPort signal and will not work with additional video adapters such as Mini DisplayPort to HDMI, Mini DisplayPort to VGA or Mini DisplayPort to DVI adapters

This adapter will not support Thunderbolt displays


Environmental

Operating Temperature 0C to 45C (32F to 113F)
Storage Temperature -10C to 70C (14F to 158F)
Humidity 10%-85%RH

Physical Characteristics

Color White
Material Plastic
Cable Length 5.5 in [14 cm]
Product Length 7.1 in [18.0 cm]
Product Width 1.1 in [27.0 mm]
Product Height 0.6 in [16.0 mm]
Weight of Product 0.8 oz [23.0 g]

Packaging



Information

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	1.1 oz [31.0 g]

What's in the Box

Included in Package	USB-C to Mini DisplayPort adapter
---------------------	-----------------------------------

****Product appearance and specifications are subject to change without notice.***

