

Fiber Optic Cable - Single-Mode Duplex 9/125 - LSZH - LC/LC - 10 m

## **Product ID: SMFIBLCLC10**



The SMFIBLCLC10 10m LC to LC Single-Mode Duplex Fiber Cable features 9/125 micron fiber for high-speed, high bandwidth data transmissions over Gigabit Ethernet and Fiber Channel networks, with support for duplex single-mode applications.

This LC-LC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire – an ideal solution for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Each Duplex 9/125 (OS1) Single-Mode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability, and is backed by our lifetime warranty.

## **Certifications, Reports and Compatibility**

## **Applications**

- Use in Gigabit Ethernet and Fiber Channel applications
- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication/Data communication
- Fiber Connections in Patch Panels, Hubs, Switches, Routers

## **Features**



- 2x LC SM male connectors
- OS1 (9/125)
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Attenuation loss meets or exceeds industry standards

• Molded connectors

Hardware

Warranty Lifetime

Fire Rating LSZH Rated (Low Smoke Zero Halogen)

Fiber Size 9/125

**Performance** 

Maximum Data Transfer

Rate

100Gbps

Cable Rating 10Gbps / 40Gbps / 100Gbps

Fiber Classification OS1

Type Single Mode

Connector(s)

Connector A Fiber Optic LC Duplex

Connector B Fiber Optic LC Duplex

**Environmental** 

Operating Temperature -20C to 60C (-4F to 140F)

Storage Temperature -20C to 60C (-4F to 140F)

Humidity 0~90% RH

Physical Characteristics

Color Yellow

Cable Length 32.8 ft [10 m]

Product Length 32.8 ft [10.0 m]



	Product Width	0.0 in [0.0 mm]
	Product Height	0.0 in [0.0 mm]
	Weight of Product	4.9 oz [140.0 g]
Packaging Information		
	Package Quantity	1
	Package Length	8.7 in [22.0 cm]
	Package Width	7.9 in [20.0 cm]
	Package Height	1.0 in [25.0 mm]
	Shipping (Package) Weight	5.3 oz [149.0 g]
What's in the Box		
	Included in Package	10m Single Mode Duplex Fiber Patch Cable LC-LC

<sup>\*</sup>Product appearance and specifications are subject to change without notice.