

USB-C to HDMI Adapter with 4K 30Hz - White

**Product ID:** CDP2HDW



This USB-C to HDMI adapter lets you to output 4K video and audio from the USB Type-C port on your laptop to an HDMI display or projector. The adapter works with USB 3.1 or Thunderbolt 3 Type-C devices that pass a DP video signal, such as your MacBook Pro, Chromebook or 2018 iPad Pro.

This video adapter is also available in black (CDP2HD).

This adapter lets you harness the video capabilities from your computer's USB-C connection, to deliver the astonishing quality of UHD to a 4K 30Hz display.

You can achieve an output resolution of up to 3840 x 2160p at 30Hz, perfect for performing high-resolution tasks. Plus, the USB-C display adapter is backward compatible with 1080p monitors and displays, making it a great accessory for any workspace application.

This HDMI converter lets you use the versatile USB Type-C port on your portable device. USB-C is a reversible connector, so you can plug it to your device in any direction. Plus, it's Thunderbolt 3 compatible, providing a hassle-free connection to your Windows or Mac-based Thunderbolt 3 computer.

This compact, lightweight USB-C video adapter is easy to carry in your laptop bag. It's ideal for BYOD (Bring Your Own Device) applications at the office and is compatible with any device that supports USB-C DP Alt Mode.

CDP2HDW is backed by a 2-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Connect your laptop to a provided HDMI display at work

- Deliver presentations from USB-C laptops to HDMI displays
- Connect an HDMI monitor to your USB-C laptop as a secondary display

## Features

- Hassle-free connection with the reversible USB-C connector
- Maximum portability with a small footprint and lightweight design
- Thunderbolt 3 port compatible
- Astonishing picture quality with support for Ultra HD video resolutions up to 4K
- 7.1 audio support

---

### Hardware

Warranty	3 Years
Ports	1
AV Input	USB-C
AV Output	HDMI - 1.4
Chipset ID	Parade - PS171 STMicroelectronics - STM32F072CBU6

---

### Performance

Video Revision	HDMI 1.4
Maximum Cable Distance To Display	49.9 ft [15.2 m]
Maximum Digital Resolutions	3840 x 2160 (Ultra HD 4K) @30hz
Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1920x1080 (High-definition 1080p) 1920x1200 2560x1440 2560x1600 3840 x 2160 (Ultra HD 4K) @30hz



Wide Screen Supported Yes

Audio Specifications HDMI - 7.1 Channel Audio

---

**Connector(s)**

Connector A USB-C (24 pin) DisplayPort Alt Mode

Connector B HDMI (19 pin)

---

**Special Notes / Requirements**

System and Cable Requirements Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.

---

**Power**

Power Source USB-Powered

---

**Physical Characteristics**

Color White

Material Plastic

Product Length 5.8 in [14.7 cm]

Product Width 0.9 in [23 mm]

Product Height 0.4 in [9 mm]

Weight of Product 0.8 oz [22 g]

---

**Packaging Information**

Package Length 8.7 in [22.1 cm]

Package Width 8.9 in [22.5 cm]

Package Height 0.5 in [12 mm]

Shipping (Package) Weight 1.1 oz [31 g]

---

**What's in the Box**

Included in Package USB-C to HDMI adapter

---



*\*Product appearance and specifications are subject to change without notice.*

