

3ft (1m) Heavy Duty Extension Cord, IEC 320 C14 to IEC 320 C13 Black Extension Cord, 15A 125V, 14AWG, Heavy Gauge Power Extension Cable, IEC 320 C14 to IEC 320 C13 AC Power Cord - UL Listed

Product ID: PXT100143



The PXT100143 C13 to C14 PDU Style Computer Power Extension Cord (3ft) features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher rated, heavier gauge cable, and connecting to Power Distribution Units (PDU).

Backed by Lifetime warranty, this PDU style extension cord/cable is designed and constructed for maximum durability.

Certifications, Reports and Compatibility



Applications

- Extend the power connection from your server to a PDU by up to 3ft

Features

- **HEAVY DUTY EXTENSION CABLE:** This 3ft (0.9m) 14AWG universal power cord with IEC 60320 C14 to IEC 60320 C13 connectors is suitable for workstations/home office Indoor use Rated to carry 125V at 15A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief on connectors for durability Fire Rating: VW-1 3 Conductor Power cable made with 100% copper wire Available in other lengths

- **SPECS:** 3ft (0.9m) AC Power Cord IEC 60320 C14 to IEC 60320 C13 14AWG 125V 15A (Max) Jacket Type: SJT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.36in (9.14mm)
- **COMPATIBILITY:** PC Power Cord C14 works with North American cables Extend connections to servers, desktop computers, monitors, printers, and more Replacement power extension cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	1 - IEC 60320 C13 Power
Connector B	1 - IEC 60320 C14 Power

Special Notes / Requirements

Note	UL Listed
------	-----------


Power

Input Voltage	125 AC
Input Current	15 A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	3.0 ft [0.9 m]
Weight of Product	5.5 oz [156 g]

Packaging Information



Package Quantity	1
Package Length	11.4 in [29 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.7 in [44 mm]
Shipping (Package) Weight	5.8 oz [163 g]

What's in the Box

Included in Package	1 - 3 ft 14 AWG Computer Power Cord Extension - C14 to C13
---------------------	--

****Product appearance and specifications are subject to change without notice.***

