

USB-C to eSATA Cable - For External Storage Devices - USB 3.0 (5Gbps) - 3 ft. (1 m)

Product ID: USB3C2ESAT3



This USB- C^{TM} to eSATA cable is an external drive adapter that gives you quick and easy access to an eSATA storage device through the USB-C or ThunderboltTM 3 port on your laptop.

Connect an Optical Disk Drive to Your Laptop

Even if your laptop doesn't have eSATA ports, the USB 3.0 to eSATA cable makes it easy to connect it to an external storage device. The cable supports connections to standard SATA hard drives (HDD) and solid-state drives (SSD).

The cable also supports connections to optical drives (ODD), enabling you to connect a CD-ROM or DVD-ROM drive to your laptop.

Efficiently Perform Drive-Management Tasks

The cable supports eSATA commands and functions such as SMART self-monitoring. It's also compatible with eSATA drive management hardware and software, such as backup utility software.



Data Sheet

When connected to a storage device housing HDD or SSD drives, the USB-C to eSATA cable lets IT professionals connect to drives for:

- Data recovery
- Repairing failing drives
- Re-using or re-purposing old drives
- Running drive diagnostics
- Disk imaging
- Backing up and archiving drives to prevent data loss
- Transferring content between the drive and the laptop

The 1-meter cable lets you set up anywhere, enabling you to perform any one of these tasks in a lab, at someone's desk or out in the field. With plug-and-play installation, it's easy to connect on any operating system, without any extra software to install.

USB3C2ESAT3 is backed by a StarTech.com 2-year warranty and free lifetime technical support.





Certifications, Reports and Compatibility











Applications

Connect an eSATA storage device to a USB-C or Thunderbolt 3 computer

Features

- Quickly access eSATA external storage devices with an SSD, HDD or ODD drive from a USB-C computer
- Perform drive management tasks
- Set up in a lab, at a desk or out in the field
- Save setup time with plug-and-play installation
- Compatible with SATA I, II and III which supports data transfer rates up to 6Gbps
- Backward compatible with USB 2.0



Data Sheet

	Warranty	2 Years
Hardware	Bus Type	USB 3.0
	Chipset ID	ASMedia - ASM1153E
	Compatible Drive Types	SATA
	Number of Drives	1
Performance	4Kn Support	Yes
	ATAPI Support	Yes
	Hot Swap Capability	Yes
	Max Drive Capacity	Currently tested with up to 10TB drives
	Maximum Data Transfer Rate	5Gbps
	Port Multiplier	No
	S.M.A.R.T. Support	Yes
	TRIM Support	No
	Type and Rate	USB 3.0 - 5 Gbit/s
		eSATA (6 Gbps)
	UASP Support	No
Connector(s)	Drive Connectors	1 - eSATA (7 pin, Data) Male
	Host Connectors	1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Male
Software	OS Compatibility	OS independent; No software or drivers required
Power	Power Source	USB-Powered
Environmental	Humidity	40%-85%RH
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Cable Length	3 ft [0.9 m]
	Color	Black
	Enclosure Type	Plastic
	Product Height	0.5 in [1.2 cm]
	Product Length	36 in [91.4 cm]
	Product Width	0.5 in [12 mm]
	Weight of Product	1.6 oz [45 g]



Data Sheet

Packaging Information	Package Height	0.7 in [17 mm]
	Package Length	9.8 in [25 cm]
	Package Width	1.3 in [34 mm]
	Shipping (Package) Weight	1.6 oz [45 g]
What's in the Box	Included in Package	1 - adapter cable
		1 - quick-start guide

Product appearance and specifications are subject to change without notice.