

Mini DisplayPort to DVI Video Adapter Converter - White

Product ID: MDP2DVIW



The MDP2DVIW passive Mini DisplayPort to DVI Adapter (White) offers an easy-to-use DVI/Mini-DisplayPort link that enables you to connect a DVI computer monitor to a device with a Mini-DisplayPort output (such as a laptop video out port) or video card. The adapter is the perfect accessory for any of your MacBook or Microsoft Surface Pro devices with mDP.

The adapter supports high resolution output up to 1920x1200, offering a cost-effective solution for mirroring or extending a computer desktop onto a second display. Plus, because the adapter functions passively, it can be used with a DVI to HDMI adapter, to connect an HDMI-equipped monitor to a Mini DisplayPort output.

This versatile Mini DisplayPort to DVI adapter requires a multimode DisplayPort port (DisplayPort ++) connection to function, and is compatible with Intel Thunderbolt output when directly connected to a supporting DisplayPort over Thunderbolt I/O port.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade shows using DVI displays
- Keep your existing DVI monitor for use with your new Mini DisplayPort device
- Ideal for using a DVI monitor as a secondary display connected through a Mini DisplayPort output

Features

- Easy to use cable, no software required
- Supports resolutions up to 1920x1200 and HDTV resolutions up to 1080p
- Compatible with Intel Thunderbolt

Hardware

Warranty	3 Years
Active or Passive Adapter	Passive
AV Input	Mini DisplayPort - 1.2
AV Output	DVI-I (Digital Only) - Single-Link
Audio	No
Industry Standards	DisplayPort 1.1a DVI 1.1

Performance

Maximum Digital Resolutions	1920x1200 / 1080p
Audio Specifications	DVI - No Audio Support
MTBF	2,205,691 hours

Connector(s)

Connector A	Mini-DisplayPort (20 pin)
Connector B	DVI-I (29 pin)

Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	40~85% RH

Physical Characteristics

Color	White
Material	Plastic



Cable Length	4.7 in [12 cm]
Product Length	7.1 in [18 cm]
Product Width	1.8 in [45 mm]
Product Height	0.6 in [15 mm]
Weight of Product	1.0 oz [29 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.6 in [15 mm]
Shipping (Package) Weight	1.5 oz [43 g]

What's in the Box

Included in Package	Mini DisplayPort to DVI Converter
---------------------	-----------------------------------

****Product appearance and specifications are subject to change without notice.***

