

4 Port USB to RS232 Serial DB9 Adapter Hub

Product ID: ICUSB2324



This 4 Port USB to RS232 Serial Hub lets you connect up to four RS232 serial devices to your Mac or PC laptop or desktop computer through a single USB port, as though the computer offered built-on DB9M serial connectors.

The RS232 Serial Hub is compactly designed to preserve valuable workspace, and is bus-powered to eliminate the need for an external power adapter.

A cost-effective solution that bridges the compatibility gap between modern USB-capable computers and legacy RS232 serial peripherals, this dependable USB/RS232 Serial Adapter hub is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect modems, digitizer tablets, mice, bar code scanners, GPS receivers, ISDN terminal adapters, mobile phones, scanners, UPSes and POS equipment to your system
- Connect and program LED and Digital signage boards with serial communication ports

Features

- Bus powered, no external power adapter required
- Easy Plug-and-Play installation
- Fully compliant with USB 1.1 specifications and compatible with USB 2.0

- Provides you with four additional RS232 serial ports

Hardware

Warranty	Lifetime
Ports	4
Interface	Serial
Bus Type	USB 2.0
Port Style	External Hub
Industry Standards	RS232
	USB 1.1
Chipset ID	FTDI - FT232RL

Performance

Serial Protocol	RS-232
Max Baud Rate	921.6 Kbps
FIFO	256 Bytes

Connector(s)

Connector Type(s)	USB Type-A (4 pin) USB 2.0
External Ports	DB-9 (9 pin, D-Sub)

Software


OS Compatibility	Windows CE (4.2, 5.0, 6.0), XP Embedded, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10
	Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019
	macOS 10.6 to 10.15, 11.0
	Linux Kernel 3.0.x - 5.4.x (LTS Versions Only)

Special Notes / Requirements

System and Cable Requirements	One free USB port
-------------------------------	-------------------

Power

Power Consumption (In	1 ~ 1.5W
-----------------------	----------



Watts)

Environmental

Operating Temperature	0C to 55C (32F to 131F)
Storage Temperature	-20 to 85C (-4 to 185F)
Humidity	5~95% RH

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	6.0 ft [1.8 m]
Product Length	5.9 in [15 cm]
Product Width	2.6 in [66.5 mm]
Product Height	1.0 in [26 mm]
Weight of Product	6.2 oz [175 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	5.9 in [15 cm]
Package Height	2.1 in [53 mm]
Shipping (Package) Weight	13.3 oz [378 g]

What's in the Box

Included in Package	4 Port Serial Hub
	USB Cable
	Mounting Bracket
	Driver CD
	Instruction Manual



****Product appearance and specifications are subject to change without notice.***

