

3ft (1m) VESA Certified DisplayPort 1.4 Cable - 8K 60Hz Video, HBR3 HDR - Super UHD DisplayPort Monitor Cable/Cord - Ultra HD 4K 120Hz Slim DP 1.4 Cable - M/M DP Connector

**Product ID:** DP14MM1M



This DisplayPort 1.4 cable connects your DisplayPort laptop or desktop computer to a “super ultra-high definition” 8K monitor, TV or projector. It supports resolutions up to 8K (7680x4320) @ 60Hz.

The DisplayPort monitor cable provides the essential connection to support the next generation of super ultra-high definition video.

This cable is VESA to ensure full compliance and efficient operation of the higher link rate of HBR3. It has been tested to meet all DP 1.4 specifications to ensure quality and reliability.

This 8K DisplayPort cable supports all DP 1.4 features:

- High Bit Rate 3 (HBR3) Bandwidths of 32.4 Gbps supporting the latest in industry standards
- High Dynamic Range (HDR) for higher contrast ratio and vivid colors
- Multi-Stream Transport (MST) for daisy-chaining multiple monitors
- Display Stream Compression 1.2 (DSC) for maximum resolution output
- Forward Error Correction to manage data transmission errors
- High-Bandwidth Digital Content Protection (HDCP 2.2) for a secure connection between source and display
- 32 Uncompressed Digital Audio Channels

The cable has a slim professional grade 34 AWG construction that allows for flexible installation while offering superior reliability for a clean quality installation. Each connector features latches that provide secure connections between your devices.

8K has a resolution of 7680 x 4320 and is also known as 4320p and Super Ultra High Definition (SUHD). It is seen in

digital signage and other commercial displays that require the highest available resolution. This cable is backward compatible with 4K and 5K displays making it the perfect peripheral to start futureproofing your cabling infrastructure.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have a broad product expertise and work directly with StarTech.com Engineers to provide support for our customers both pre and post-sales.

DP14MM1M is backed by a StarTech.com lifetime warranty.

## Certifications, Reports and Compatibility

### Applications

- Delivering visually enriched presentations
- Displaying crisp digital signage walls
- Creating eye-catching visuals for photography, videography, cinematography
- Producing lifelike gaming

### Features

- **FUTURE PROOF:** Upgraded version of DISPLPORT3L/DSPL1M supports DISPLAYPORT 1.4; VESA Certified DisplayPort cable; 32.4Gbps bandwidth; 8K 60Hz (7680x4320), 4K 120Hz (3840x2160), HDR, HBR3, 32ch audio, FEC error control
- **RELIABLE:** DisplayPort 1.4 cable is built with internal wire manager to ensure signal integrity; Metal connector sub-structure provides EMI shielding; Latching DP connectors prevent accidental disconnection
- **DURABLE:** PVC jacket of this slim DisplayPort monitor cable absorbs stress of frequent bends protecting the core of the DisplayPort cord; Gold plated connectors prevent oxidization and tarnish, Lifetime Warranty
- **APPLICATIONS:** Super UHD video cable ideal for professional workstations w/Radeon Vega Frontier/Pro WX Series/W5500/Pro Duo & Nvidia Quadro; Compatible w/DP 1.1/1.2/1.3 (1080p/4K) cards & adapters to future-proof for 8K
- **SPECS:** 1m (3.3 ft) Black DisplayPort 1.4 DP Male to Male 34 AWG Jacket: PVC EMI Shielding Supported Protocols: HBR 3, 4:4:4 Chroma Subsampling, DSC 1.2, HDCP 2.2, MST Lifetime Warranty

---

#### Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Gold

Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	VW-1 Rated

---

**Connector(s)**

Connector A	DisplayPort (20 pin)
Connector B	DisplayPort (20 pin)

---

**Physical Characteristics**

Color	Black
Connector Style	Latching
Wire Gauge	34 AWG
Product Length	39.4 in [100.0 cm]
Product Width	0.5 in [12.0 mm]
Product Height	0.4 in [10.0 mm]
Weight of Product	2.1 oz [59.0 g]

---

**Packaging Information**

Package Length	8.7 in [22.0 cm]
Package Width	7.8 in [19.8 cm]
Package Height	0.0 in [1.0 mm]
Shipping (Package) Weight	2.4 oz [69.0 g]

---

**What's in the Box**

Included in Package	DisplayPort Cable
---------------------	-------------------

---

*\*Product appearance and specifications are subject to change without notice.*

