

1U Fixed Server Rack Mount Shelf - 10in Deep Steel Universal Cantilever Tray for 19" AV/ Network Equipment Rack - Heavy Duty Steel - Weight Capacity 44lbs/20kg, Black

Product ID: CABSHELF1U10



This 1U rack shelf lets you add 10 in. of flat storage space to any EIA-310 compliant server rack or cabinet.

The durable fixed-rack shelf can hold up to 20 kg (44 lbs.) of equipment and is constructed using SPCC commercial-grade cold-rolled steel.

The 1U cantilever shelf lets you optimize your working space by giving you the ability to mount equipment to your rack instead of taking up desk or floor space. It's perfect for your SOHO (small office, home office) environment, server room or any other location with limited space available.

You can install the 1U rack shelf in your rack at any height, giving you a stable surface for placing equipment that's un-mountable or storing your tools.

The CABSHELF1U10 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

• Supply additional storage space for mission-critical hardware and non-rackmount equipment

Features

• EIA-310 compliant

• UNIVERSAL COMPATIBILITY: 19" EIA/ECA-310 compliant 1U 10" deep server rack cabinet shelf for universal fit in any existing server/AV rack or cabinet & includes M6 Cage nuts & screws for mounting shelf



• DURABLE DESIGN: Heavy-duty cantilever shelf tray that is easy to install, constructed of durable 16 gauge SPCC commercial cold-rolled steel with support for weight up to 44 lbs with lifetime warranty

• FLEXIBLE INSTALLATION: The rack mount cantilever shelf can be mounted in 2 orientations, install the shelf with the front shelf lip downwards or mount with the lip upwards to prevent your computer, AV or other equipment & accessories from sliding off

• INSTALLS IN ANY RACK BRAND: The shelf is fully compatible w/ the full array of StarTech.com server/network cabinets & enclosures (4POSTRACK12U, RK2236BKF) & other brands like: HP, APC, Dell & Lenovo

• LIFETIME WARRANTY: StarTech.com offers 24 hour technical support & has been the choice of IT professionals for 30 years, conducting thorough compatibility & performance testing on all products

Hardware		
	Warranty	Lifetime
	Frame Type	Steel
	U Height	1U
	Cable Management	No
	Industry Standards	EIA/ECA-310-E
Performance	Weight Capacity (Stationary)	44.2 lb [20 kg]
Special Notes / Requirements	Note	Includes 4x C-cup washers
Physical Characteristics		
Characteristics	Color	Black
	Material	Steel
	Internal Width	17.4 in [44.3 cm]
	Product Length	9.8 in [25 cm]
	Product Width	18.3 in [46.5 cm]
	Product Height	1.7 in [43 mm]
	Weight of Product	4.4 lb [2.0 kg]



Packaging

Information		
	Package Length	19.8 in [50.3 cm]
	Package Width	11.3 in [28.6 cm]
	Package Height	2.3 in [58 mm]
	Shipping (Package) Weight	5.4 lb [2.5 kg]
What's in the Box		
What's in the Box	Included in Package	1U Fixed Shelf
	Included in Package	1U Fixed Shelf M6 Cage Nuts
	Included in Package	

*Product appearance and specifications are subject to change without notice.

