

USB to DVI Adapter - 1920x1200

Product ID: USB2DVIPRO2



The USB2DVIPRO2 USB to DVI Adapter functions as an external graphics card for Windows and Mac computers - the perfect solution for turning your desktop or laptop computer into a dual or multi-monitor environment, all through the simplicity and convenience of USB.

The USB-DVI Adapter delivers high quality video (up to 1920x1200) for a variety of applications and is capable of simultaneously running up to five additional displays from a single computer (using four USB2DVIPRO2 External Video Adapters). The adapter connects to a host computer through a USB 2.0 port, acting as an external DVI video card to either extend or mirror the desktop shown on the existing display - without having to open the computer case.

Featuring driver support for Microsoft Windows (including Aero themes) and Mac OS X, and with video support for resolutions up to 1920x1200, this USB-DVI video adapter is the ideal solution for a wide range of operating environments as well as large-screen displays/monitors.

The USB2DVIPRO2 USB to DVI Adapter is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Add multiple (up to five) monitors / projectors to your computer setup using one USB2DVIPRO2 device for each additional display
- View large or multiple spreadsheets across multiple displays
- Increase productivity by running multiple applications on different DVI screens; check your email on one display while editing a document on the other

- Use the USB-DVI adapter to connect your PC to your television for showing family pictures and movies
- Connect multiple DVI monitors to a single computer to create engaging multimedia presentations
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- Support for Aero themes in Windows
- Works with Mac OS X
- Optimal performance at 1920x1200 and ideal for use with 24" to 26" monitors or smaller
- USB-Powered operation, no external power adapter required
- Quick and easy installation
- Powered by DisplayLink DL-195 chip

Hardware

Warranty	2 Years
AV Input	USB 2.0
AV Output	DVI
USB Pass-Through	No
Memory	16MB
Chipset ID	DisplayLink - DL-195

Performance

Maximum Digital Resolutions	1920x1200 (32-bit color)
Supported Resolutions	Widescreen (16/32 bit): 1920x1200, 1680x1050, 1440x900, 1366x768 Standard (16/32 bit): 1600x1200, 1280x1024, 1024x768, 800x600, 640x480
General Specifications	This USB video adapter uses a DisplayLink family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a Trigger

or Fresco family chipset.

MTBF 621,445 Hours

Connector(s)

Connector Type(s) DVI-I (29 pin)
USB Type-A (4 pin) USB 2.0

Software

OS Compatibility Windows XP (32-bit), Vista, 7, 8, 8.1, 10
macOS 10.6 - 10.12, 10.14 - 10.15, 11.0
Chrome OS v55+
Ubuntu 14.04, 16.04, 18.04

Special Notes / Requirements

System and Cable Requirements System Processor: 1.2GHz
System Memory: 512MB

Note Power PC-based Macintosh computers, such as late-model iMacs, PowerBooks and PowerMacs, are not currently supported

This USB video adapter uses a DisplayLink family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as Trigger or Fresco Logic

Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources

This USB video adapter is not intended for graphical intensive applications, such as gaming

Indicators

LED Indicators Blue - Power

Power

Power Source USB-Powered

Environmental

Operating Temperature 10C to 40C (50F to 104F)

Storage Temperature -10C to 80C (14F to 176F)



Humidity <85% non-condensing

Physical Characteristics

Color	Black
Cable Length	6.5 in [16.5 cm]
Product Length	10.6 in [27 cm]
Product Width	2.2 in [55 mm]
Product Height	0.8 in [20 mm]
Weight of Product	2.5 oz [70 g]

Packaging Information

Package Length	5.7 in [14.6 cm]
Package Width	8.3 in [21.1 cm]
Package Height	1.7 in [42 mm]
Shipping (Package) Weight	8.6 oz [245 g]

What's in the Box

Included in Package	USB to DVI Adapter
	DVI to VGA adapter
	Driver CD
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

