

Stock Code: **20076LEDD-BRZ/ACR**

Collection: **Ulko**

**PRODUCT INFORMATION**

Base: 20076 Parent: 20076LEDD  
Mounting Type: Ceiling UPC: 641594224573  
Finish: Bronze  
Diffuser: Acrylic Lens

**PRODUCT MEASUREMENTS**

|                 |                           |
|-----------------|---------------------------|
| <b>FIXTURE</b>  | <b>BACKPLATE / CANOPY</b> |
| Length: 9"      | Length                    |
| Width: 9"       | Width:                    |
| Diameter        | Diameter:                 |
| Height: 1"      | Height:                   |
| Extension:      |                           |
| Overall Height: |                           |

**TECHNICAL SPECIFICATIONS**

**SPECIFICATIONS**

Frame Material: Acrylic  
Diffuser Material: Acrylic  
Lamping Type: SSL (Dedicated LED) Jbox: Standard  
Lamping Base: SSL Lamp Wattage: 20 W  
Lamp Quantity: 1 Total Wattage: 20 W  
Voltage: 120v Lamps Included: Yes

**QUALIFICATIONS**

Location Rating Wet  
Certification: ETL (US/Canada) Listed  
ADA Compliant: No Energy Star: No  
JA8 Compliant: Outdoor Only Emergency Lighting: No  
Marine Grade: No Warranty: 5 Year

**PHOTOMETRICS**

Dimmable: Yes Nominal Lumens 1800 Lm  
CRI: 90 Delivered Lumens: 1349 Lm  
CCT: 3000K  
Recommended Dimmers:  
(TRIAC)LEVITON Trimatron 6684; (MLV)LUTRON Diva DVLV-600P; (TRIAC)LUTRON Diva DV-600P; (ELV)LUTRON Skylark SELV-300P; (TRIAC)LUTRON Diva DVCL-153P; (TRIAC)LEVITON Decora Sureslide 6674; (TRIAC)LEVITON Surslide 6631


**Additional Notes:**

Optional Color Temperature 200 Piece Minimum Order Quantity;  
Custom Finish 200 Piece Minimum Order Quantity

Project Name: \_\_\_\_\_  
Location: \_\_\_\_\_  
Type: \_\_\_\_\_  
Quantity: \_\_\_\_\_  
Notes: \_\_\_\_\_



**LINE DRAWING**



**IES FILE**

In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: \_\_\_\_\_

Print Name \_\_\_\_\_ Date: \_\_\_\_\_

**Toll Free 800-828-5483 www.AccessLighting.com**

14410 Myford Road, Irvine, CA 92606

