

Stock Code: **20350LEDDMGLP-SAT/CLR**

Collection: KO

### PRODUCT INFORMATION

Base: 20350 Parent: 20350LEDDMGL  
Mounting Type: Wall UPC: 641594200652  
Finish: Satin  
Diffuser: Clear

### PRODUCT MEASUREMENTS

| FIXTURE         | BACKPLATE / CANOPY |
|-----------------|--------------------|
| Length:         | Length             |
| Width: 4.25"    | Width:             |
| Diameter        | Diameter:          |
| Height: 4.25"   | Height: 1.5"       |
| Extension: 4"   |                    |
| Overall Height: |                    |

### TECHNICAL SPECIFICATIONS

#### SPECIFICATIONS

Frame Material: Aluminum  
Diffuser Material: Glass  
Lamping Type: GU-10 (Replaceable LE Jbox: Standard  
Lamping Base: GU-10 Lamp Wattage: 5.3 W  
Lamp Quantity: 1 Total Wattage: 5.3 W  
Voltage: 120v Lamps Included: Yes

#### QUALIFICATIONS

Location Rating Wet  
Certification: UL (US/Canada) Listed  
ADA Compliant: Yes Energy Star: No  
JA8 Compliant: No Emergency Lighting: No  
Marine Grade Finish: Yes  
Warranty: 5 Year

#### PHOTOMETRICS

Dimmable: Yes Nominal Lumens 346 Lm  
CRI: 80 Delivered Lumens: N/A  
CCT: 3000K  
Recommended Dimmers:  
(TRIAC)LEVITON Surslide 6631; (TRIAC)LEVITON Trimatron 6684; (TRIAC)LUTRON Ariadni/Toggler TGCL-153P; (TRIAC)LUTRON Skylark S-600 or S-600P; (TRIAC)LUTRON Diva DV-600P

#### ADDITIONAL NOTES

Can be Mounted Bulb Up or Bulb Down; Custom Finish 100 Piece Minimum Order Quantity

Project Name: \_\_\_\_\_

Location: \_\_\_\_\_


Type: \_\_\_\_\_

Quantity: \_\_\_\_\_

Notes: \_\_\_\_\_



#### LINE DRAWING



#### IES FILE

In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: \_\_\_\_\_

Print Name \_\_\_\_\_ Date: \_\_\_\_\_

Toll Free 800-828-5483 [www.AccessLighting.com](http://www.AccessLighting.com)

14410 Myford Road, Irvine, CA 92606

The information is subject to change without notice. 12/22/2022 20350LEDDMGLP-SAT\_CLR.pdf

