


# NYLON WIRE TIES



These nylon wire ties offer a secure solution for all of your cable and wire bundling installations. The BLACK Nylon Wire Ties are suitable for outdoor use.



## FEATURES

18-120 lbs. Tensile Strength (Refer to Page 2)

Durable Nylon Construction

UV Rated for Outdoor Use (BLACK ONLY)

Limited Lifetime Warranty

## Product Specifications

	0E-WT418B	0E-WT850N
	0E-WT418B5	0E-WT850N10
	0E-WT418N	0E-WT12120B
	0E-WT418N5	0E-WT12120N
	0E-WT55540N	0E-WT1250B
<b>PART #</b>	0E-WT55540B	0E-WT1250B5
	0E-WT8120B	0E-WT1250N
	0E-WT8120N	0E-WT1250N5
	0E-WT850B	0E-WT1450B
	0E-WT850B10	0E-WT1450B5

Length: 4", 5.5", 8", 12", 14"

Color: Black, Natural

Package Quantity: 100, 500, 1000



For more information contact your  
ADI Sales person or visit  
[adiglobal.com/adiexclusivebrands](http://adiglobal.com/adiexclusivebrands)

# NYLON WIRE TIES

ADI Part #	Description	Length	Tensile Strength (Pounds)	Package Quantity
0E-WT418B	Black Nylon Wire Ties	4"	18	100
0E-WT418B5	Black Nylon Wire Ties	4"	18	500
0E-WT418N	Natural Nylon Wire Ties	4"	18	100
0E-WT418N5	Natural Nylon Wire Ties	4"	18	500
0E-WT55540N	Natural Nylon Wire Ties	5.5"	40	100
0E-WT55540B	Black Nylon Wire Ties	5.5"	40	100
0E-WT8120B	Black Nylon Wire Ties	8"	120	100
0E-WT8120N	Natural Nylon Wire Ties	8"	120	100
0E-WT850B	Black Nylon Wire Ties	8"	50	100
0E-WT850B10	Black Nylon Wire Ties	8"	50	1,000
0E-WT850N	Natural Nylon Wire Ties	8"	50	100
0E-WT850N10	Natural Nylon Wire Ties	8"	50	1,000
0E-WT12120B	Black Nylon Wire Ties	12"	120	100
0E-WT12120N	Natural Nylon Wire Ties	12"	120	100
0E-WT1250B	Black Nylon Wire Ties	12"	50	100
0E-WT1250B5	Black Nylon Wire Ties	12"	50	500
0E-WT1250N	Natural Nylon Wire Ties	12"	50	100
0E-WT1250N5	Natural Nylon Wire Ties	12"	50	500
0E-WT1450B	Black Nylon Wire Ties	14"	50	100
0E-WT1450B5	Black Nylon Wire Ties	14"	50	500

For more information contact your ADI Sales person.

