

Stock Code: **62537LEDDCS-MBL/ACR**

Collection: Retreat

### PRODUCT INFORMATION

Base: 62537 Parent: 62537LEDD  
Mounting Type: Wall UPC: 641594248449  
Finish: Matte Black  
Diffuser: Acrylic Lens

### PRODUCT MEASUREMENTS

| FIXTURE          | BACKPLATE / CANOPY |
|------------------|--------------------|
| Length:          | Length             |
| Width: 36"       | Width:             |
| Diameter         | Diameter:          |
| Height: 4.5"     | Height:            |
| Extension: 3.25" |                    |
| Overall Height:  |                    |

### TECHNICAL SPECIFICATIONS

#### SPECIFICATIONS

Frame Material: Metal  
Diffuser Material: Acrylic  
Lamping Type: SSL (Dedicated LED) Jbox: Standard  
Lamping Base: SSL Lamp Wattage: 30 W  
Lamp Quantity: 1 Total Wattage: 30 W  
Voltage: 120v Lamps Included: Yes

#### QUALIFICATIONS

Location Rating: Damp  
Certification: ETL (US/Canada) Listed  
ADA Compliant: Yes Energy Star: No  
JA8 Compliant: Yes Emergency Lighting: No  
Marine Grade Finish: No  
Warranty: 5 Year

#### PHOTOMETRICS

Dimmable: Yes Nominal Lumens: 2400 Lm  
CRI: 90 Delivered Lumens: N/A  
CCT: Multi-CCTK  
Recommended Dimmers:  
(ELV)LUTRON Maestro CL MACL-153M; (ELV)LUTRON  
Maestro MRF2-6CL; (TRIAC)LUTRON Diva DVCL-153P;  
(ELV)LUTRON Caseta PD - 6WCL

#### ADDITIONAL NOTES

Horizontal and Vertical Mounting; 3 CCT Selectable Switch  
2700K, 3000K, 4000K

Project Name: \_\_\_\_\_

Location: \_\_\_\_\_

Type: \_\_\_\_\_


Quantity: \_\_\_\_\_

Notes: \_\_\_\_\_



#### LINE DRAWING

#### IES FILE



In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: \_\_\_\_\_

Print Name \_\_\_\_\_ Date: \_\_\_\_\_

Toll Free 800-828-5483 [www.AccessLighting.com](http://www.AccessLighting.com)

14410 Myford Road, Irvine, CA 92606

The information is subject to change without notice.

1/7/2023

62537LEDDCS-MBL\_ACR.pdf

**access**  
LIGHTING