

# L&Z BRACKETS

## FOR 600 LB. MAGNETIC LOCKS

**ADI**  
**PRO**

This professional grade L&Z bracket is finished in anodized aluminum. It is the perfect solution for installing 600 lb. magnetic locks on in-swinging, single doors: use the L bracket to mount the magnet to the vertical face of the frame when there is no space on the header, and use the Z bracket to horizontally adjust the armature plate.



## FEATURES


**For use with ADI PRO 600 lb. Magnetic Locks**

**Brushed Aluminum Finish (US28)**

**For use on in-swinging, single doors**

**Heavy-duty, vandal resistant construction**

**2-Year Warranty**



## Product Specifications

**UPC:** 811914029939

**PART #:** 0E-LZB6

### L Bracket Dimensions (W x H x D):

9-7/8" x 2-1/16" x 1-5/16"  
(250mm x 52mm x 34mm)

### Z Bracket Dimensions (W x H x D):

7-1/8" x 4-1/4" x 2-1/8"  
(181mm x 108mm x 54mm)

**For more information contact your ADI Sales person or visit [adiglobal.com/adiexclusivebrands](http://adiglobal.com/adiexclusivebrands)**

# SUPPORTS L&Z

POUR SERRURE MAGNÉTIQUE DE 600 LB. (LIVRES)

**ADI**  
**PRO**

Ce support professionnel de grade L&Z est fini en aluminium anodisé. C'est la solution parfaite pour installer des serrure magnétique de 600 lb. (livres) sur des portes simples s'ouvrant vers l'intérieur: utilisez le support en L pour monter les serrure magnétique sur la face verticale du cadre lorsqu'il n'y a pas d'espace sur l'entête, et utilisez le support en Z pour ajuster horizontalement la plaque d'armature.



## CARACTÉRISTIQUES

Pour une utilisation avec des serrure magnétique ADI PRO de 600 livres

Finition en aluminium brossé (US28)

Pour une utilisation sur les portes s'ouvrant vers l'intérieur

Construction résistante aux actes de vandalisme

Garantie de 2 ans

## Spécifications du produit

UPC: 811914029939


NUMÉRO DE PIÈCE: 0E-LZB6

Dimensions du support en L (L x H x P):

9-7/8po x 2-1/16po x 1-5/16po  
(250mm x 52mm x 34mm)

Dimensions du support en Z (L x H x P):

7-1/8po x 4-1/4po x 2-1/8po  
(181mm x 108mm x 54mm)



Pour de plus amples renseignements, communiquez avec un représentant ADI ou visitez la page [fr.adiglobaldistribution.ca](http://fr.adiglobaldistribution.ca)