



GREEN EPOXY COATED WIRE SHELVING



with
Optional Casters

Item #: _____ Qty #: _____
 Model #: _____
 Project #: _____

WIRE SHELVING

GREEN EPOXY POSTS


GREEN EPOXY POSTS WITH ADJUSTABLE FOOT

Numbered Posts



| MODEL # | Post Height | Boxed Weight |
|---------|-------------|--------------|
| EGP-14 | 14" | 4 lbs. |
| EGP-34 | 34" | 8 lbs. |
| EGP-54 | 54" | 12 lbs. |
| EGP-64 | 64" | 15 lbs. |
| EGP-74 | 74" | 17 lbs. |
| EGP-86 | 86" | 20 lbs. |

GREEN EPOXY POSTS FOR CASTERS



Rubber
Caster

Poly
Caster

| MODEL # | Post Height | Post Height with Casters | Boxed Weight |
|---------|-------------|--------------------------|--------------|
| EGPC-14 | 14" | 20" | 4 lbs. |
| EGPC-34 | 34" | 40" | 8 lbs. |
| EGPC-54 | 54" | 60" | 12 lbs. |
| EGPC-64 | 64" | 70" | 15 lbs. |
| EGPC-74 | 74" | 80" | 17 lbs. |
| EGPC-86 | 86" | 92" | 20 lbs. |

Posts are packed 4 to a box.

FEATURES:

Each shelf holds up to 800 lbs. evenly distributed weight.
 NSF approved for dry storage and wet environments only.
 Posts are numbered for easy assembly

CONSTRUCTION:

Unit assembles using tapered split sleeves.
 For mobile units, 5" swivel Rubber or Poly casters includes set of 4 casters, (2 with brakes) and 4 donut bumpers.
 set of 4 casters, (2 with brakes) and 4 donut bumpers.

MATERIAL:

Zinc plated wire with green epoxy coating.

| MODEL # | Shelf Size | Boxed Weight |
|----------|------------|--------------|
| EG-1424 | 14" x 24" | 35 lbs. |
| EG-1430 | 14" x 30" | 41 lbs. |
| EG-1436 | 14" x 36" | 47 lbs. |
| EG-1442 | 14" x 42" | 52 lbs. |
| EG-1448 | 14" x 48" | 58 lbs. |
| *EG-1460 | 14" x 60" | 38 lbs. |
| *EG-1472 | 14" x 72" | 45 lbs. |
| EG-1824 | 18" x 24" | 39 lbs. |
| EG-1830 | 18" x 30" | 45 lbs. |
| EG-1836 | 18" x 36" | 51 lbs. |
| EG-1842 | 18" x 42" | 56 lbs. |
| EG-1848 | 18" x 48" | 64 lbs. |
| *EG-1854 | 18" x 54" | 35 lbs. |
| *EG-1860 | 18" x 60" | 41 lbs. |
| *EG-1872 | 18" x 72" | 49 lbs. |
| EG-2124 | 21" x 24" | 41 lbs. |
| EG-2130 | 21" x 30" | 48 lbs. |
| EG-2136 | 21" x 36" | 55 lbs. |
| EG-2142 | 21" x 42" | 63 lbs. |
| EG-2148 | 21" x 48" | 70 lbs. |
| *EG-2154 | 21" x 54" | 41 lbs. |
| *EG-2160 | 21" x 60" | 45 lbs. |
| *EG-2172 | 21" x 72" | 48 lbs. |
| EG-2424 | 24" x 24" | 44 lbs. |
| EG-2430 | 24" x 30" | 51 lbs. |
| EG-2436 | 24" x 36" | 58 lbs. |
| EG-2442 | 24" x 42" | 64 lbs. |
| EG-2448 | 24" x 48" | 72 lbs. |
| *EG-2454 | 24" x 54" | 41 lbs. |
| *EG-2460 | 24" x 60" | 47 lbs. |
| *EG-2472 | 24" x 72" | 55 lbs. |

24" to 48" length shelves are packed 4 to a box and
 *54", 60" and 72" shelves are packed 2 to a box.

OPTIONAL ACCESSORIES

| | MODEL # | Qty |
|------------------------------|---------|-----|
| 5" Rubber Swivel Stem Caster | EC-25 | |
| 5" Poly Swivel Stem Caster | EC-26 | |



Customer Service Available To Assist You 1-800-645-3166 8:30 am - 7:00 pm E.S.T.

For Orders & Customer Service:

Email: customer@advancetabco.com or Fax: 631-242-6900

For Smart Fabrication™ Quotes:

Email: smartfab@advancetabco.com or Fax: 631-586-2933

DETAILS and SPECIFICATIONS

TOL \pm .500"

ALL DIMENSIONS ARE TYPICAL

