



18 GA. STAINLESS STEEL WORK TABLES

TTS Series





Fully Adjustable Leg Collar



	18" WIDE			24" WIDE			30" WIDE		
L	Model	Approx. Wt.	Approx. Cu. Ft.	Model	Approx. Wt.	Approx. Cu. Ft.	Model	Approx. Wt.	Approx. Cu. Ft.
24"	TTS-182-X	27 lbs.	2	TTS-242-X	36 lbs.	2			
30"	TTS-180-X	30 lbs.	2	TTS-240-X	40 lbs.	2	TTS-300-X	50 lbs.	3
36"	TTS-183-X	33 lbs.	3	TTS-243-X	44 lbs.	2	TTS-303-X	55 lbs.	3
48"	TTS-184-X	38 lbs.	3	TTS-244-X	52 lbs.	3	TTS-304-X	64 lbs.	4
60"	TTS-185-X	42 lbs.	4	TTS-245-X	60 lbs.	4	TTS-305-X	73 lbs.	5
72"	TTS-186-X	48 lbs.	5	TTS-246-X	68 lbs.	4	TTS-306-X	82 lbs.	5
84"				TTS-247-X*	75 lbs.	5			
96"	TTS-188-X*	60 lbs.	7	TTS-248-X*	88 lbs.	9	TTS-308-X*	105 lbs.	11

^{*7&#}x27; and 8' tables furnished with 6 legs

ltem #:	Qty #:
Model #:	
Project #: _	

FEATURES:

Top is furnished with 1 5/8" sanitary rolled rim on front and rear; and square ends.

Two die formed hat channels are attached to underside of work table top to reinforce and maintain a level working surface.

Leg Collar at undershelf corner secures leg shelf to legs and is fully adjustable.

CONSTRUCTION:

All TIG welded. Exposed weld areas polished to match adjacent surface.

Top is sound deadened.

Die formed galvanized hat channels are secured to top by means of structural adhesive and weld studs.

Gussets welded to hat channels.

MATERIAL:

TOP: 18 Gauge Stainless Steel Type "430" Series

SHELF: 18 Gauge Stainless Steel

with Stainless Steel Gussets


LEGS: 1 5/8" Diameter Tubular Stainless Steel Steel

1" Stainless Steel Legs & Bullet Feet

DETAILS and SPECIFICATIONS

TOL ± .500"

ALL DIMENSIONS ARE TYPICAL





Customer Service Available To Assist You 1-800-645-3166 8:30 am - 7:00 pm E.S.T.

For Orders & Customer Service:

For Smart Fabrication™ Quotes:

Email: smartfab@advancetabco.com or Fax: 631-586-2933