



STAINLESS STEEL EQUIPMENT FILLER TABLE

Item #:	_____	Qty #:	_____
Model #:	_____		
Project #:	_____		



**TFMS Series
w/ Open Base**



**TFMSU Series
w/ Adjustable Undershef**

FEATURES:

TOP is furnished with 1 5/8" sanitary rolled rim edge in front. Square edges on sides and 1/1/2" splash of single metal thickness on rear. Hat channels stud welded to top which reinforces and maintains a level working surface. Welded Front to Back Leg Assembly. Rear (Left to Right) Stretcher bolts to side leg assemblies. Aluminum die cast "leg-to-shelf" clamp secures shelf to leg eliminating unsightly nuts and bolts. Undershef is fully adjustable.

CONSTRUCTION:

All TIG welded. Exposed weld areas polished to match adjacent surfaces. Entire top mechanically polished to a satin finish. Top is sound deadened. Roll formed embossed galvanized hat channels are secured to top by means of structural adhesive and weld studs. Gussets welded to support hat sections.

MATERIAL:

TOP: 16 gauge stainless steel type "304" series.
SHELF: 16 gauge stainless steel type "304" series.
STRETCHERS: 1 5/8" diameter tubular stainless steel.
LEGS: 1 5/8" diameter tubular stainless steel. Stainless steel gussets. 1" stainless steel bullet feet.

OPEN BASE

Model	L	W	Wt.	Cu. Ft.
TFMS-122	12"	24"	21 lbs.	2
TFMS-120		30"	22 lbs.	3
TFMS-123		36"	29 lbs.	3
TFMS-152	15"	24"	22 lbs.	2
TFMS-150		30"	24 lbs.	3
TFMS-153		36"	31 lbs.	3
TFMS-182	18"	24"	23 lbs.	2
TFMS-180		30"	25 lbs.	3
TFMS-183		36"	32 lbs.	3

W/ ADJ. UNDERSHELF

Model	L	W	Wt.	Cu. Ft.
TFMSU-152	15"	24"	24 lbs.	2
TFMSU-150		30"	29 lbs.	2
TFMSU-153		36"	41 lbs.	3
TFMSU-182	18"	24"	29 lbs.	2
TFMSU-180		30"	33 lbs.	2
TFMSU-183		36"	52 lbs.	3



Customer Service Available To Assist You 1-800-645-3166 8:30 am - 7:00 pm E.S.T.

For Orders & Customer Service:
 Email: customer@advancetabco.com or Fax: 631-242-6900


For Smart Fabrication™ Quotes:
 Email: smartfab@advancetabco.com or Fax: 631-586-2933

DIMENSIONS and SPECIFICATIONS

TOL \pm .500"

ALL DIMENSIONS ARE TYPICAL

TFMS Series w/ Open Base



TFMSU Series w/ Adjustable Undershelf

