



ISO-9001 Registered Quality System.  
ISO-21469 Compliant.

### Sales, Service & Distribution Center

Newark, NJ 07105  
Phone: 973-589-9150 Fax: 973-589-4432

### Manufacturing, Sales, Service & Distribution Center

Toledo, OH 43605  
Phone: 419-691-2491 Fax: 419-693-3806

### Sales and Tech Service Support

Phone: 1-800-733-4755

## PRODUCT DATA

# LUBRIPLATE GENERAL PURPOSE FOOD GRADE SILICONE LUBRICANT (AEROSOL)

"This product is certified OU Kosher Pareve"  
"This product is Halal certified"

\*NSF International H-1 Registered  
NSF ISO21469 Certification

## DESCRIPTION

A high yield silicone aerosol that provides an odorless, colorless and stainless protective film. LUBRIPLATE General Purpose Food Grade Silicone Lubricant displays excellent benefits when used on rubber or metal molds as a release agent.

## APPLICATIONS

LUBRIPLATE General Purpose Food Grade Silicone Lubricant is a proven food grade silicone lubricant used in processing, packaging and packing equipment. All the components in this product comply with FDA 21 CFR 178.3570 and are NSF International H-1 Registered.

## ADVANTAGES

- ⇒ Film provides rust, corrosion and tarnish resistance. Contains 20% silicone which delivers a stronger and longer-lasting protective film compared to competitive products in the marketplace.
- ⇒ Water resistance.
- ⇒ Wide operating temperature range.

### STORAGE RECOMMENDATIONS

1. Products should be stored between 40°F-120°F.
2. Products should be stored in a dry covered environment.
3. Products should not be stored in warm, direct sunlight.
4. improper storage conditions can significantly alter the shelf life of the product. Such conditions would include temperature, moisture, open containers, etc.



## Typical Test Data

| PROPERTY                | TEST METHOD | TYPICAL RESULTS*         |
|-------------------------|-------------|--------------------------|
| Appearance              | Visual      | Crystal Clear Liquid     |
| Specific Gravity @ 25°C | ASTM D-287  | 0.968                    |
| Flash Point             | ASTM D-92   | >600°F (Base Fluid Only) |
| Flash Point             | ASTM D-92   | <0°F (Propellant)        |
| Pour Point              | ASTM D-97   | Minus 65°C               |

### Cautions:

*Due to the high silicone content per spray, use sparingly to avoid excess buildup. Product is packaged as an aerosol. Follow all safety precautions on label.*

## PACKAGING AVAILABLE

## Part No.

12/9.5 oz. Aerosol Cans

L0723-063

*Note: Also available in Bulk form under Product Name - LUBRIPLATE Silicone Fluid FG-350. For more information, see Technical Data Bulletin - 8-31.*

**\*NSF International H-1 Registration No.**  
(Meets former USDA 1998 Guidelines)

**126086**

*\*Registered H-1 by NSF International for use in food processing facilities as a lubricant or anti-rust agent on equipment in which there may be incidental contact involving the lubricated part and the edible product.*

*"LUBRIPLATE General Purpose Food Grade Silicone Lubricant contains no components derived from TSE/BSE relevant animal species; therefore, it is compliant with the requirements of the TSE Note for Guidance EMA/410/01 Rev. 3 July 2011".*