


3 MM POWERHOUSE™ TIMING PULLEY FLANGES


(Compatible with PowerGrip® GT2® and PowerGrip® GT3® pitches)

**3 mm Pitch
Aluminum**




Timing Pulley Flanges

Part Number	Metric				Inch			
	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness
10-3P-FA	6.2 mm	12.8 mm	0.6 mm	1.1 mm	0.244"	0.505"	0.025"	0.045"
11-3P-FA	6.9 mm	13.5 mm	0.6 mm	1.1 mm	0.270"	0.530"	0.025"	0.045"
12-3P-FA	8.2 mm	14.7 mm	0.6 mm	1.1 mm	0.322"	0.580"	0.025"	0.045"
13-3P-FA	8.9 mm	15.5 mm	0.6 mm	1.1 mm	0.350"	0.610"	0.025"	0.045"
14-3P-FA	9.5 mm	16.1 mm	0.8 mm	1.3 mm	0.374"	0.635"	0.032"	0.052"
15-3P-FA	10.8 mm	17.4 mm	0.8 mm	1.3 mm	0.426"	0.685"	0.032"	0.052"
16-3P-FA	11.5 mm	18.0 mm	0.8 mm	1.3 mm	0.452"	0.710"	0.032"	0.052"
17-3P-FA	11.5 mm	18.8 mm	0.8 mm	1.3 mm	0.452"	0.740"	0.032"	0.052"
18-3P-FA	12.8 mm	20.1 mm	0.8 mm	1.3 mm	0.504"	0.790"	0.032"	0.052"
19-3P-FA	13.5 mm	20.7 mm	0.8 mm	1.3 mm	0.530"	0.815"	0.032"	0.052"
20-3P-FA	14.6 mm	22.7 mm	0.8 mm	1.3 mm	0.574"	0.895"	0.032"	0.052"
22-3P-FA	15.9 mm	24.0 mm	0.8 mm	1.3 mm	0.626"	0.945"	0.032"	0.052"
24-3P-FA	17.9 mm	26.0 mm	0.8 mm	1.3 mm	0.704"	1.025"	0.032"	0.052"
25-3P-FA	18.7 mm	26.9 mm	0.8 mm	1.3 mm	0.738"	1.060"	0.032"	0.052"
26-3P-FA	19.7 mm	28.1 mm	0.8 mm	1.3 mm	0.774"	1.105"	0.032"	0.052"
28-3P-FA	21.6 mm	29.8 mm	0.8 mm	1.3 mm	0.849"	1.173"	0.032"	0.052"
30-3P-FA	23.5 mm	31.8 mm	0.8 mm	1.3 mm	0.924"	1.250"	0.032"	0.052"
32-3P-FA	25.4 mm	33.6 mm	0.8 mm	1.3 mm	0.999"	1.323"	0.032"	0.052"
34-3P-FA	27.3 mm	35.5 mm	1.0 mm	1.5 mm	1.074"	1.398"	0.040"	0.060"
36-3P-FA	29.2 mm	37.4 mm	1.0 mm	1.5 mm	1.149"	1.473"	0.040"	0.060"
38-3P-FA	31.1 mm	39.3 mm	1.0 mm	1.5 mm	1.225"	1.549"	0.040"	0.060"
40-3P-FA	33.0 mm	41.3 mm	1.0 mm	1.5 mm	1.300"	1.625"	0.040"	0.060"
44-3P-FA	36.8 mm	45.1 mm	1.0 mm	1.5 mm	1.450"	1.775"	0.040"	0.060"



For matching 3 mm
POWERHOUSE™ pitch
timing pulleys,
see page 128.



For matching 3 mm
POWERHOUSE™ pitch
timing belts,
see page 233.