




POWERHOUSE MX™ TIMING PULLEYS

(Compatible with Poly Chain® GT® Carbon belts)

8 mm Pitch
For 21 mm Wide Belts
Flanges
Steel/Iron
Black Oxide Plating
Taper-Lock® Style



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bushing	Face Width (in)	Overall Length (in)
22-8MX21-1008	22	A1F	2.206	2.143	2.559	1008	1.203	1.203
25-8MX21-1108	25	A1F	2.506	2.443	2.953	1108	1.203	1.203
26-8MX21-1108	26	A1F	2.607	2.544	2.953	1108	1.203	1.203
27-8MX21-1108	27	A1F	2.707	2.644	3.150	1108	1.203	1.203
28-8MX21-1108	28	A1F	2.807	2.744	3.150	1108	1.203	1.203
29-8MX21-1108	29	A1F	2.907	2.844	3.346	1108	1.203	1.203
30-8MX21-1108	30	A1F	3.008	2.945	3.346	1108	1.203	1.203
31-8MX21-1210	31	A1F	3.108	3.045	3.543	1210	1.203	1.203
32-8MX21-1210	32	A1F	3.208	3.145	3.543	1210	1.203	1.203
33-8MX21-1610	33	A1F	3.308	3.245	3.819	1610	1.203	1.203
34-8MX21-1610	34	A1F	3.409	3.346	3.819	1610	1.203	1.203
35-8MX21-1610	35	A1F	3.509	3.446	3.938	1610	1.203	1.203
36-8MX21-1610	36	A1F	3.609	3.546	3.938	1610	1.203	1.203
37-8MX21-1610	37	A1F	3.709	3.646	4.156	1610	1.203	1.203
38-8MX21-1610	38	A1F	3.810	3.747	4.156	1610	1.203	1.203
39-8MX21-1610	39	A1F	3.910	3.847	4.331	1610	1.203	1.203
40-8MX21-2012	40	A1F	4.010	3.947	4.331	2012	1.250	1.250
41-8MX21-2012	41	A1F	4.110	4.047	4.331	2012	1.250	1.250
42-8MX21-2012	42	A1F	4.211	4.148	4.687	2012	1.250	1.250
45-8MX21-2012	45	A1F	4.511	4.448	5.005	2012	1.250	1.250
48-8MX21-2012	48	A1F	4.812	4.749	5.157	2012	1.250	1.250
50-8MX21-2012	50	A1F	5.013	4.950	5.320	2012	1.250	1.250
53-8MX21-2012	53	A1F	5.314	5.251	5.625	2012	1.250	1.250
56-8MX21-2012	56	A1F	5.614	5.551	5.945	2012	1.250	1.250
60-8MX21-2012	60	A1F	6.015	5.952	6.375	2012	1.250	1.250
63-8MX21-2012	63	C1F	6.316	6.253	6.772	2012	1.203	1.250
67-8MX21-2517	67	C1F	6.717	6.654	7.231	2517	1.203	1.750
71-8MX21-2517	71	C1F	7.118	7.055	7.575	2517	1.203	1.750
72-8MX21-2517	72	C1F	7.218	7.155	7.575	2517	1.203	1.750
75-8MX21-2517	75	C1F	7.519	7.456	7.867	2517	1.203	1.750
80-8MX21-2517	80	C1F	8.020	7.957	8.386	2517	1.203	1.750
90-8MX21-2517	90	C2	9.023	8.960	-	2517	1.203	1.750
112-8MX21-2517	112	C2	11.229	11.166	-	2517	1.203	1.750
140-8MX21-2517	140	C3	14.036	13.973	-	2517	1.203	1.750
180-8MX21-2517	180	C3	18.046	17.983	-	3020	1.203	2.000
224-8MX21-3020	224	C3	22.457	22.394	-	3020	1.203	2.000



For matching 8MX pitch belts, see page 248.