

Project:	AIA#
Item:	
Location:	SIS#
Approved:	

MODEL:

HBR35HC-1

HORIZON BOTTOM MOUNT REACH-IN

HBR35HC Solid Door Reach-in Refrigerator Hydrocarbon Series



3 Year Parts/Labor Warranty Additional 4 Year Compressor Warranty

CABINET CONSTRUCTION

- Stainless steel front, side, and grille (galvanized back & bottom)
- Stainless steel interior
- LED lighting
- Full electronic control with one-touch defrost
- One–piece grille allow easy removal/installation for preventative maintenance
- Door lock (solid doors only)
- Self closing door with 120° stay open feature
- Spring-loaded style hinges
- Plug-in magnetic door gaskets
- Three (3) heavy duty epoxy coated wire shelves per door section
- 6" Casters with two (2) brakes

OPTIONS & ACCESSORIES

- 3" caster or 6" legs
- Epoxy shelves
- Shelf clips
- Remote option* (see note on back page)

REFRIGERATION SYSTEM

- Uses environmentally friendly, energy efficient R290 refrigerant, and meets all regulatory requirements for CARB, SNAP, DOE & more
- Adaptive defrost
- Epoxy coated evaporator coil
- Refrigerator capable of maintaining product temperatures between 36°F and 38°F



3779 Champion Blvd., Winston-Salem, NC 27105 1-888-845-9800 Fax: 1-336-245-6453 Beverage-Air.com Sales@bevair.com




BEVERAGE-AIR.

MODEL	HBR35HC-1	
EXTERNAL DIMENSIONAL DATA		
Width Overall	39 1⁄2"	
Depth Overall with Handle	33 1⁄4″	
Height Overall with Casters	84"	
Number of Doors	2	
Depth with Door Open 90°	49 ⁷ ⁄8"	
Door Opening (in)	16 ½" x 52 ⁵⁄ଃ"	
INTERNAL DIMENSIONAL DATA		
NET Capacity (cubic ft.)	36.87	
Internal Width Overall (in)	36 ⅔″	
Internal Depth Overall (in)	25 %"	
Internal Height Overall (in)	61 5⁄8″	
Internal Height Useable (in)	52 7⁄8″	
Number of Shelves	6	
ELECTRICAL DATA		
Full Load Amperes 115/60/1	2.4	
REFRIGERATION DATA		
Horsepower*	1/4	
Capacity (BTU/Hr)*	1702	
SHIPPING DATA		
Gross Weight - Crated	480 lbs	
Height - Crated	85"	
Width - Crated	36"	
Depth - Crated	34"	
NOTE: Remote units are field wired and come	with 6" legs.	

Refrigerant must be specified at time of order.

Bottom Mount Reach-In Refrigerator Model: HBR35HC-1



***ELECTRICAL CONNECTION**



Unit pre-wired at factory and include 8' long cord and plug set.

3779 Champion Blvd., Winston-Salem, NC 27105 1-888-845-9800 Fax: 1-336-245-6453 Beverage-Air.com Sales@bevair.com

an Ali Group Company

G R O U P The Spirit of Excellence

