



# BEVERAGE-AIR

Project: \_\_\_\_\_

AIA#

Item: \_\_\_\_\_

Location: \_\_\_\_\_

SIS#

Approved: \_\_\_\_\_

## SPE ELITE SERIES FOOD PREPARATION TABLES

MODELS:

### SPE48HC Mega Top Sandwich Prep Table

SPE48HC-18M

### Hydrocarbon Series



SPE48HC-18M

**3 Year Parts/Labor Warranty**  
**Additional 4 Year Compressor Warranty**

### CABINET CONSTRUCTION

- Stainless steel front, sides, top, doors and grille (*galvanized steel back & bottom*)
- Interior liner is made of corrosion resistant aluminum
- Removable hoods and insulated lid assemblies are made of matching stainless steel
- Self-closing doors with 120° Stay-open feature, on cartridge style hinges
- Easy door removal for service and cleaning
- Field-reversible doors with snap-in door gaskets
- Painted aluminum door handles
- 6" Casters, with (2) brakes standard
- 10" Wide cutting board constructed of white polyethylene plastic
- Cutting board removable for cleaning
- Two epoxy-coated steel wire shelves per section standard
- Pans furnished are 4" deep constructed of polycarbonate plastic
- Enhanced airflow maintains temperature between 36° to 38°F

### OPTIONS & ACCESSORIES

- Stainless steel back
- Stainless steel interior
- Right or left hinged
- Locks (doors only)
- Overshelves (single or double)
- Crumb catcher
- 6" legs or 3" casters available
- Low profile casters
- Richlite & composite cutting board
- Night cover
- Shelf dividers
- Pan Supports
- Digital / stem dial thermometer
- Remote option

### REFRIGERATION SYSTEM

- Refrigeration system uses R290 refrigerant to comply with all environmental concerns
- Automatic, non-electric defrost
- Epoxy coated evaporator coil

SPE48HC Elite Series Sandwich Prep: Mega Top Series




3779 Champion Blvd., Winston-Salem, NC 27105  
1-888-845-9800 Fax: 1-336-245-6453  
Beverage-Air.com sales@bevair.com



# BEVERAGE-AIR

| MODEL                                     | SPE48HC-18M                    |
|---|--------------------------------|
| <b>EXTERNAL DIMENSIONAL DATA</b>          |                                |
| Width Overall                             | 48"                            |
| Depth Overall with Cutting Board & Bumper | 38 3/8"                        |
| Height Overall with 6" Casters            | 49"                            |
| Number of Doors                           | 2                              |
| Depth with Door Open 90°                  | 52 1/4"                        |
| Solid Door Opening (in)                   | 19 5/8" x 21 5/8"              |
| Depth, Cutting Board                      | 10"                            |
| <b>INTERNAL DIMENSIONAL DATA</b>          |                                |
| NET Capacity (cubic ft.)                  | 13.01                          |
| Internal Width Overall (in)               | 44"                            |
| Internal Depth Overall (in)               | 23 1/2"                        |
| Internal Depth Useable (in)               | Upper 18 1/2"<br>Lower 15 3/8" |
| Internal Height Overall (in)              | 23"                            |
| Internal Height Useable (in)              | 17 5/8"                        |
| Number of Shelves                         | 4                              |
| Number of Pans                            | (18) 1/6                       |
| <b>ELECTRICAL DATA</b>                    |                                |
| Full Load Amperes 115/60/1                | 2.2                            |
| <b>REFRIGERATION DATA</b>                 |                                |
| Horsepower                                | 1/6                            |
| Capacity (BTU/Hr)*                        | 1094                           |
| <b>WEIGHT DATA</b>                        |                                |
| Gross Weight (Crated lbs)                 | 336 lbs                        |
| Height - Crated                           | 48"                            |
| Width - Crated                            | 51"                            |
| Depth - Crated                            | 38"                            |

## Food Preparation Table — Mega Top Models: SPE48HC-18M



### ELECTRICAL CONNECTION



115/60/1  
NEMA-5-15P

Units pre-wired at factory and include 8' long cord and plug set.



an Ali Group Company



The Spirit of Excellence

3779 Champion Blvd., Winston-Salem, NC 27105  
1-888-845-9800 Fax: 1-336-245-6453  
Beverage-Air.com sales@bevair.com