



AMERICAN EAGLE[®]
FOOD MACHINERY, INC.

AE-BS06
AE-BS01/AE-BS02
Countertop
Bread Slicers

773.376.0800 (P) • 773.376.2010 (F) • 3131 S. Canal St. Chicago, IL 60616

Lower Your Total Cost of Ownership with American Eagle[®] Bread Slicers! Top Reliability And Competitive Pricing Make Us The Value Leader in the Industry.

Quality Design On All Models

- All Stainless Steel Food Contact Surfaces, Durable Heat Treated Alloy Steel Blades
- Heavy Duty Steel Frame, NSF Approved Paint Finish Resists Rust, Scratches, and Dents
- Fixed Blade Design, Available In A Large Range Of Sizes: 3/8", 1/2", 5/8", 3/4", 1.0" Cuts
- Maintenance Free Belt Drive, Thermal Overload Helps Protects Motor
- 1 Year Limited Warranty*



AE-BS06



AE-BS06, Our Proven, Time Tested, Best Selling Model!

- Durable 1/4 HP Motor
- Simple Gravity Fed Design Minimizes Moving Parts



AE-BS01***

AE-BS01, Our Premium Model With Extra Safety Features

- Powerful 1/2HP Motor
- Advanced, Single Motion Lever Design Closes Safety Guard, Starts Machine, Then Feeds Loaf Into Blades
- Bread Crumb Drawer Keeps Work Area Clean

AE-BS02, Our Advanced Model With Push Button Start / Stop

- Powerful 1/2HP Motor
- Push Button Start, Emergency Stop Button
- Lever Pushes Loaf Into Blades
- Bread Crumb Drawer Keeps Work Area Clean



AE-BS02***

Proud Member of:

 North American Association of
 Food Equipment Manufacturers

Quality • Value • Reliability



AMERICAN EAGLE[®]
FOOD MACHINERY, INC.

AE-BS06
AE-BS01/AE-BS02
Countertop
Bread Slicers

sales@ameagle.biz • www.americaneaglemachine.com

American Eagle® Bread Slicers are ideal for supermarket bakeries and retail bake shops! They offer excellent performance and value for your money. A variety of available cut sizes allow you to choose the perfect slicer. They are simple to operate and slice through all types of bread from crusty artisan to soft sandwich!

Detailed Specifications

Model	Feed Type	Loaves/ Minute	Max Loaf Length	Motor	Voltage V/HZ/PH	Amps	Cut Sizes Available**	Bagging Shelf	Crumb Drawer	Safety Guard
AE-BS06	Gravity	4	14.75"	1/4 HP	115/60/1	3	3/8", 1/2", 5/8" 3/4", 1.0"	No	No	No
AE-BS02	Push Lever	7.5	15.0"	1/3 HP	115/60/1	4	3/8", 1/2", 5/8" 3/4", 1.0"	Yes	Yes	No
AE-BS01	Push Lever	7.5	15.0"	1/2 HP	115/60/1	7	3/8", 1/2", 5/8" 3/4", 1.0"	Yes	Yes	Yes

Save Time and Labor Costs, Bring In Repeat, Satisfied Customers!

Unlike manual slicing, our bread slicers help maintain the bread's proper shape, and allows easy training of new employees in a bakery operation. Bread slicing is a great value added service!

Dimensions and Shipping Information

Model	Overall Dimensions	Net Weight	Shipping Dimensions****	Ship Weight	Freight Class
AE-BS06	24.8"W x 24.8L" x 27.0"H (63cm x 63cm x 69cm)	154 lbs (70 kg)	27"W x 30"L x 31.5"H (69cm x 76cm x 80cm)	199 lbs (91 kg)	85
AE-BS02***	23.5"W x 23.5"L x 24.75"H (60cm x 60cm x 63cm)	176 lbs (80 kg)	27.5"W x 31"L x 32"H (70cm x 79cm x 82cm)	240 lbs (109 kg)	85
AE-BS01***	30"W x 30.5"L x 32.6"H (76cm x 72cm x 83cm)	253 lbs (115 kg)	34.25"W x 33.75"L x 35.25"H (87cm x 86cm x 90cm)	324 lbs (147 kg)	85

*Warranty must be registered. Improper Installation will void warranty

**Size is fixed and not adjustable. Must be chosen at time of order

***Special Order Item. Normal Lead Time is 6-8 weeks for manufacturing/delivery

****Crates are affixed to a skid (pallet). The weight and dimensions of this skid are included above and may vary from shipment to shipment.



Quality • Value • Reliability