



PREMIUM COPPER-BASED ANTI-SEIZE LUBRICANT

PART NO. **NSCU**

DESCRIPTION

NSCU is our premium anti-seize compound, composed of pure copper and large flake graphite in a high-heat-resistant carrier, fortified with the latest in rust and corrosion inhibitors and antioxidants. It is designed to lubricate and protect threaded connections and flanges at temperatures up to 1800°F (982°C) and under extreme load pressure conditions. Meets the performance requirements of MIL-PRF-907F.

GENERAL PROPERTIES

Technology / Base	Anti-Seize Lubricant
Components	One Component
Curing	Non-Curing/Hardening
Appearance/Color	Copper
Consistency	Paste



FEATURES & BENEFITS

- Protects parts from seizing, galling, rust and corrosion
- Resistant to high temperature applications
- Aids in assembly and disassembly of parts
- Highly resistant to salt water and galvanic corrosion
- Compatible with all types of metals and most plastics

INSTRUCTIONS

Clean surfaces before applying. Do not dilute compound. Apply to parts with brush and assemble. Straighten brush to remove last bit of compound. Keep container sealed when not using. Not for use on oxygen systems.

STORAGE

Stated shelf life can be achieved when product is stored in a tightly sealed container in a cool dry place. If slight separation occurs, stir product.

SPECIFICATIONS & APPROVALS

MIL-PRF-907F

HANDLING & CLEANUP

See SDS for handling and cleanup information.

SAFETY & DISPOSAL

See SDS for safety and disposal information.

DISCLAIMER

IMPORTANT: The information, specifications, procedures and recommendations herein (together "information") are based on our experience and we believe these to be accurate. No representation, guarantee or warranty is made as to the accuracy or completeness of the information or that the information will avoid losses or damages or give desired results. It is user's sole responsibility to test and determine the suitability of any product for the intended use. Tests should be repeated if materials or conditions change in any way. The user is advised to review the specific context of the intended use to determine whether the user's intended use violates any law or infringes upon any patent(s). No employee, distributor or agent has any right to change these facts and offer a guarantee of performance.

NOTE TO USER: by ordering/receiving product you accept the **H.B. Fuller General Terms and Conditions of Sale** applicable in the region. Please request a copy if you have not received these. These Terms and Conditions contain disclaimers of implied warranties (including but not limited to disclaiming warranties of fitness for a particular purpose) and limits of liability. All other terms are rejected. In any event, (1) the total aggregate liability of H.B. Fuller for any claim or series of related claims however arising, in contract, tort (including negligence), breach of statutory duty, misrepresentation, strict liability or otherwise, is limited to replacement of affected products or refund of the purchase price for affected products. (2) H.B. Fuller shall not be liable for loss of profit, loss of margin, loss of contract, loss of business, loss of goodwill or any indirect or consequential losses arising out of or in connection with product supply.

Unless otherwise noted, trademarks are property of H.B. Fuller Company or one of its affiliated entities. Gorilla and GorillaPro are registered trademarks of The Gorilla Glue Company.
© H.B. Fuller Company, 2022.

PHYSICAL PROPERTIES (UNCURED)

Specific Gravity	1.2
Penetration	300
Penetration Method	ISO 2137, 1/10mm
Oil Separation	1%
Oil Separation Conditions	30 hr at 158°F
Flash Point	>350°F
Flash Point Method	ASTM D92-85 (IP 36/65)
Friction Coefficient	0.1
Torque Coefficient, K Value	0.15 ± 0.02
Torque Coefficient Note	Test individual fasteners to determine exact K values and specific application performance.
Salt Fog Corrosion	168 hours
Salt Fog Corrosion Method	ASTM B117
Solid Lubricants	39%
Service Temperature	-287°F to 1800°F (-177°C to 980°C)
Shelf Life	5 years

TDS - Anti-Seize Lubricant - NSCU - Updated 11-10-2021



GorillaPro.com

9001 W. Fey Dr. · Frankfort, IL 60423 · +1-888-676-7763
SUPPORT: 1-888-MRO-PROF, gorillapro@hbfuller.com



H.B. Fuller