



## SKU # MS240WCWA

Part # 1007247

### Description

New - 49.25inch Single Row Marine Grade Wrap Around White Shell Light Bar with 240-Watt 24 x 10W High Intensity OSRAM LEDs



**Categories** Marine, Marine Sport Lighting

### Sub-Categories

Marine Sport® Heavy Duty Single Row LED Light Bars, Marine Series Light Bars

**UPC** 817999028799

**Unit of Measure** EA

### Related Skus:

### Cross Sell Skus:

### Condition

New

### Manufacturer

Marine Sport Lighting

### EZ Category

Marine Single Row Curve Bar

### Harmonization Code

8512.20.2080

### Universal

YES

### Life Expectancy

**SEMA Product** Light Bar

**Part Type ID** 1069

### Reverse Polarity

Light Bar

### Operating Voltage

12-32VDC

### Current Draw

19A

### Wattage

240-Watts

### Chip Type

### IP Rating

IP67

### LUX

### Product Information

The NEW Marine Sport LED Light Bars are a revolutionary way to contour light bars and high power light output to any surface area with a straight or curve appeal. The light bars are designed for Marine use, but can also be used in Automotive, UTV, ATV, Industrial applications where a white colored shell is desired. To make these bars even more attractive, Race Sport uses a white facing tile instead of the common chrome tiles to give this a TRUE "WHITE OUT" look! We use durable and long lasting CREE 3-watt diodes in these bars and recess them in our long throw opticals for a maximum performance and light output! . Operating Voltage: 9-30V DC 10 watt OSRAM . Color Temperature: 6000K . Lens material: PC . Optional Beam: Combo . Waterproof Rate to 1M : IP67 . Optional Color: Black . Material: Aluminum alloy painting . Mounting Bracket: Alu firm bracket . 50000+ hours life-span 49.25in End-to-End 48.0in Lens Width Area 50.50in Mounting Hole to Mounting Hole 3.0in Height 3.5in Depth Not

**Est. Labor** 1 Hours

**Gross Weight** 13.38 **Width** 6.00

**Net Weight** 11.44 **Height** 7.00

**DIM Weight** 15.71 **Depth** 52.00

### Kelvin (ColorTemperature)

6,500K

### Universal or Vehicle Specific

Universal

### Made In

China

### Warranty

3 year

### Lumens

14,900lm

### Beam Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

[www.racesportinc.com](http://www.racesportinc.com)