

MXL TIMING BELTS

0.080" Pitch


Standard Widths:

1/8", 3/16", 1/4", 3/8"

Neoprene Construction

Fiberglass Reinforcements

(Note: Custom belt widths are available upon request.)



Part Number	No. of Teeth	Pitch Length (in)
147MXL	147	11.760
148MXL	148	11.840
149MXL	149	11.920
150MXL	150	12.000
151MXL	151	12.080
153MXL	153	12.240
154MXL	154	12.320
155MXL	155	12.400
156MXL	156	12.480
158MXL	158	12.640
159MXL	159	12.720
160MXL	160	12.800
162MXL	162	12.960
163MXL	163	13.040
164MXL	164	13.120
165MXL	165	13.200
166MXL	166	13.280
167MXL	167	13.360
169MXL	169	13.520
170MXL	170	13.600
171MXL	171	13.680
175MXL	175	14.000
177MXL	177	14.160
180MXL	180	14.400
184MXL	184	14.720
186MXL	186	14.880
188MXL	188	15.040
190MXL	190	15.200
192MXL	192	15.360
194MXL	194	15.520
195MXL	195	15.600
196MXL	196	15.680
200MXL	200	16.000

Part Number	No. of Teeth	Pitch Length (in)
204MXL	204	16.320
205MXL	205	16.400
208MXL	208	16.640
210MXL	210	16.800
212MXL	212	16.960
215MXL	215	17.200
216MXL	216	17.280
220MXL	220	17.600
221MXL	221	17.680
222MXL	222	17.760
224MXL	224	17.920
225MXL	225	18.000
226MXL	226	18.080
228MXL	228	18.240
229MXL	229	18.320
230MXL	230	18.400
232MXL	232	18.560
234MXL	234	18.720
235MXL	235	18.800
236MXL	236	18.880
239MXL	239	19.120
240MXL	240	19.200
243MXL	243	19.440
245MXL	245	19.600
248MXL	248	19.840
249MXL	249	19.920
250MXL	250	20.000
251MXL	251	20.080
255MXL	255	20.400
256MXL	256	20.480
260MXL	260	20.800
262MXL	262	20.960
265MXL	265	21.200

Part Number	No. of Teeth	Pitch Length (in)
267MXL	267	21.360
268MXL	268	21.440
271MXL	271	21.680
273MXL	273	21.840
275MXL	275	22.000
280MXL	280	22.400
285MXL	285	22.800
288MXL	288	23.040
290MXL	290	23.200
295MXL	295	23.600
297MXL	297	23.760
298MXL	298	23.840
300MXL	300	24.000
305MXL	305	24.400
308MXL	308	24.640
310MXL	310	24.800
312MXL	312	24.960
315MXL	315	25.200
318MXL	318	25.440
320MXL	320	25.600
323MXL	323	25.840
324MXL	324	25.920
326MXL	326	26.080
328MXL	328	26.240
330MXL	330	26.400
332MXL	332	26.560
334MXL	334	26.720
335MXL	335	26.800
336MXL	336	26.880
337MXL	337	26.960
339MXL	339	27.120
340MXL	340	27.200
342MXL	342	27.360

Neoprene MXL timing belt part numbers can be determined as follows:
 Tooth Count + MXL + Width Code + (G for fiberGlass reinforcement)
 Example: 194MXL025G