



Portable **Cast Iron** Hot Plates - **120V**

Made in America



Infinite Heat Controls



CDR-2CFB
Double Cast Iron
Space Saver Hot Plate
Space saving front-to-back design
7-1/2" cast iron elements
900W/burner / 1,800W total / 120V

NEMA 5-20P

CDR-2C
Double Cast Iron Hot Plate
7-1/2" cast iron elements
900W/burner / 1,800W total / 120V

All Models:
● **Cast Iron Elements**
● **Heavy Duty Stainless Construction**

Also Available



Made in Germany



KR-1:
Cast Iron Hot Plate
(Same as KR-S2, except Black Enamel Finish)

KR-S2:
Cast Iron Hot Plate
7-1/8" element / 1500W / 120V

COMMON FEATURES

- Heavy duty cast iron element(s)
- Solid elements deliver heat evenly to pot/pan
- High-tech thermostat offers sensitive variable heat control to keep food simmering or boiling
- Signal light glows only during heat cycle
- Compact size saves precious counter space
- Metal housing with easy to clean surface
- Full one year warranty covering parts and labor
- Non-skid feet ● 120V ● NEMA 5-15P plug
- UL Safety & Sanitary / C-UL ● Freight class 200

● NOTE: Max load capacity of 15 pounds per burner.

If using a stockpot or braising pan, no larger than a 1" overhang over element diameter.

NEMA
5-15P
Plug

NEMA
5-20P
Plug

Model	Color	Volts	Watts	Amps	Unit Dimensions	Unit Wt.	Ship Wt.	Carton Dimensions	Cube	UPC#
CDR-2CFB	Stainless	120	1800	15	w:13 1/2", h:4 1/8", d:22 3/4"	16 lbs.	20 lbs.	w:16 1/4", h:9 1/4", d:27 3/4"	2.4	654796-64211-3
CDR-2C	Stainless	120	1800	15	w:21 1/4", h:4 1/8", d:12 3/16"	14.4 lbs.	20 lbs.	w:23 3/8", h:8", d:16 3/4"	1.74	654796-64206-9
CSR-1CH	Stainless	120	1500	12.5	w:15 3/8", h:7 1/2", d:15"	9.5 lbs.	15 lbs.	w:17 1/2", h:11", d:17 1/2"	2	654796-61106-5
KR-S2	Stainless	120	1500	12.5	w:11 1/2", h:3", d:14"	7.2 lbs.	9 lbs.	w:13 5/8", h:4", d:15 3/4"	.5	654796-64201-4
KR-1	Black	120	1500	12.5	w:11 1/2", h:3", d:14"	7.2 lbs.	9 lbs.	w:13 5/8", h:4", d:15 3/4"	.5	654796-64000-3

For more information, please contact Cadco, Ltd, 200 International Way, Winsted, CT 06098
Tel. (860)738-2500 ● Fax (860) 738-9772 ● E-mail: info@cadco-ltd.com ● Web site: cadco-ltd.com