



**SKU # MS20WSRS**

**Part # 1007246**

Description

6.25 inch Marine Grade Single Row Straight Light Bar with 20-Watt 2 x 10W High Intensity OSRAM LEDs



**Categories** Marine, Marine Sport Lighting

**Sub-Categories**

Marine Sport® Heavy Duty Single Row LED Light Bars, Marine Series Light Bars

**UPC** 817999028683

**Unit of Measure** EA

**Related Skus:**

**Cross Sell Skus:**

**Condition**

New

**Manufacturer**

Marine Sport Lighting

**EZ Category**

Marine Single Row Straight Bars

**Harmonization Code**

8512.20.2080

**Universal**

YES

**Life Expectancy**

**SEMA Product** Light Bar

**Part Type ID** 1069

**Reverse Polarity**

Light Bar

**Operating Voltage**

12-32VDC

**Current Draw**

1.58A

**Wattage**

20-Watts

**Chip Type**

**IP Rating**

IP67

**LUX**

**Product Information**

The NEW Marine Sport LED Light Bars are a revolutionary way to contour light bars and high power light output to any surface area with a straight or curve appeal. The light bars are designed for Marine use, but can also be used in Automotive, UTV, ATV, Industrial applications where a white colored shell is desired. To make these bars even more attractive, Race Sport uses a white facing tile instead of the common chrome tiles to give this a TRUE "WHITE OUT" look! We use durable and long lasting CREE 3-watt diodes in these bars and recess them in our long throw opticals for a maximum performance and light output! . Operating Voltage: 9-30V DC 10 watt OSRAM . Color Temperature: 6000K . Lens material: PC . Optional Beam: Combo . Waterproof to 1M Rate: IP67 . Optional Color: Black . Material: Aluminum alloy painting . Mounting Bracket: Alu firm bracket . 50000+ hours life-span 6.25in End-to-End 4in Lens Width Area 7.5in Mounting Hole to Mounting Hole 3in Height 3.5in Depth Note\*\*\* MSLB

**Est. Labor** 1 Hours

**Gross Weight** 2.88 **Width** 5.25

**Net Weight** 2.31 **Height** 6.00

**DIM Weight** 2.38 **Depth** 10.50

**Kelvin (ColorTemperature)**

6,500K

**Universal or Vehicle Specific**

Universal

**Made In**

China

**Warranty**

3 year

**Lumens**

1,440lm

**Beam**

Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)