

Material	Pieces	Includes	Case	EDP No.
Tap & Hexagon Die Set				
TAPS: HSS (USA) DIES: Carbon (Import)	23 pcs (UNC & UNF)	Taps & Dies: 9/16-12, 9/16-18, 5/8-11, 5/8-18, 3/4-10, 3/4-16, 7/8-9, 7/8-14, 1-8, 1-12 & 1/4-18 (NPT). Also: 1/4" to 1" Adjustable Tap Wrench.	Wood	2000H25
TAPS: HSS (USA) DIES: Carbon (Import)	36 pcs (UNC & UNF)	Taps & Dies: 4-40, 6-32, 8-32, 10-24, 10-32, 12-24, 1/4-20, 1/4-28, 5/16-18, 5/16-24, 3/8-16, 3/8-24, 7/16-14, 7/16-20, 1/2-13, 1/2-20, & 1/8-27 (NPT). Also: 1/4" to 1" Adjustable Tap Wrench, #0 to 3/8" T-Handle Tap Wrench.	Wood	2000H38
TAPS: HSS (USA) DIES: Carbon (Import)	58 pcs (UNC & UNF)	Taps & Dies: 4-40, 6-32, 8-32, 10-24, 10-32, 12-24, 1/4-20, 1/4-28, 5/16-18, 5/16-24, 3/8-16, 3/8-24, 7/16-14, 7/16-20, 1/2-13, 1/2-20, 9/16-12, 9/16-18, 5/8-11, 5/8-18, 3/4-10, 3/4-16, 7/8-9, 7/8-14, 1-8, 1-12, & 1/8-27, 1/4-18 (NPT). Also: #7 to 1/2" & 1/4" to 1" Adjustable Tap Wrench, #0 to 3/8" T-Handle Tap Wrench.	Wood	2000H63
TAPS: HSS (USA) DIES: Carbon (Import)	18 pcs (UNC)	Taps & Dies: 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 3/4. Also: #7 to 1/2 Adjustable Tap Wrench, #12 to 1/2" T-Handle Tap Wrench.	Wood	2000HC20
TAPS: HSS (USA) DIES: Carbon (Import)	18 pcs (UNF)	Taps & Dies: 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 3/4. Also: #7 to 1/2 Adjustable Tap Wrench, #12 to 1/2" T-Handle Tap Wrench.	Wood	2000HF20
Tap & Round Adjustable Die Set				
High Speed Steel TAPS: USA DIES: Import	25 pcs (UNC & UNF)	Taps & Dies: 9/16-12, 9/16-18, 5/8-11, 5/8-18, 3/4-10, 3/4-16, 7/8-9, 7/8-14, 1-8, 1-12 & 1/4-18 (NPT). Also: 2" Round Die Stock, 1/4" to 1" Adjustable Tap Wrench, and 1 Screwdriver.	Wood	2000R25
High Speed Steel TAPS: USA DIES: Import	38 pcs (UNC & UNF)	Taps & Dies: 4-40, 6-32, 8-32, 10-24, 10-32, 12-24, 1/4-20, 1/4-28, 5/16-18, 5/16-24, 3/8-16, 3/8-24, 7/16-14, 7/16-20, 1/2-13, 1/2-20 & 1/8-27 (NPT). Also: 1" Round Die Stock, 1/4" to 1" Adjustable Tap Wrench, #0 to 3/8" T-Handle Tap Wrench and 1 Screwdriver.	Wood	2000R38
High Speed Steel TAPS: USA DIES: Import	63 pcs (UNC & UNF)	Taps & Dies: 4-40, 6-32, 8-32, 10-24, 10-32, 12-24, 1/4-20, 1/4-28, 5/16-18, 5/16-24, 3/8-16, 3/8-24, 7/16-14, 7/16-20, 1/2-13, 1/2-20, 9/16-12, 9/16-18, 5/8-11, 5/8-18, 3/4-10, 3/4-16, 7/8-9, 7/8-14, 1-8, 1-12, & 1/8-27, 1/4-18 (NPT). Also: 1" & 2" Round Die Stock, #7 to 1/2" & 1/4" to 1" Adjustable Tap Wrench, #0 to 3/8" T-Handle Tap Wrench and 2 Screwdrivers.	Wood	2000R63
High Speed Steel TAPS: USA DIES: Import	20 pcs (UNC)	Taps & Dies: 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 3/4. Also: 1-1/2" Round Die Stock, #7 to 1/2 Adjustable Tap Wrench, #12 to 1/2" T-Handle Tap Wrench, and 1 Screwdriver.	Wood	2000RC20
High Speed Steel TAPS: USA DIES: Import	20 pcs (UNF)	Taps & Dies: 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 3/4. Also: 1-1/2" Round Die Stock, #7 to 1/2 Adjustable Tap Wrench, #12 to 1/2" T-Handle Tap Wrench, and 1 Screwdriver.	Wood	2000RF20

Tap & Die Sets



2000H38



2800E36

Material	Pieces	Includes	Case	EDP No.
Pipe Tap & Die Set				
Carbon	12 pcs (NPT)	Taper Pipe Taps: 1/8-27, 1/4-18, 3/8-18, 1/2-14, 3/4-14, 1 - 11-1/2. Hexagon Pipe Dies: 1/8-27, 1/4-18, 3/8-18, 1/2-14, 3/4-14, 1 - 11-1/2.	Plastic	2700C12
Tap & Die Set				
High Speed Steel	40 pcs (UNC & UNF)	4-40 thru 1/2", Round Adjustable Dies	Plastic	2000E40
Carbon	36 pcs (Metric)	5mm thru 12mm, Round Adjustable and Hex Dies	Plastic	2800C36
High Speed Steel	36 pcs (Metric)	5mm thru 12mm, Round Adjustable Dies	Plastic	2800E36
Hexagon Die Sets (Dies Only)				
High Speed Steel	20 pcs (UNC & UNF)	1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 3/4, 7/8, & 1"	Wood	3300E20
High Speed Steel	10 pcs (UNC)	1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 3/4, 7/8, & 1"	Wood	3300EC10
High Speed Steel	10 pcs (UNF)	1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 3/4, 7/8, & 1"	Wood	3300EF10
Carbon	20 pcs (UNC & UNF)	1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 3/4, 7/8, & 1"	Wood	3350C20
Carbon	10 pcs (UNC)	1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 3/4, 7/8, & 1"	Wood	3350CC10
Carbon	10 pcs (UNF)	1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 3/4, 7/8, & 1"	Wood	3350CF10



3300EC10



3350C20

Dies