

# Drill Sets

## Jobber Drill Sets



400N29



450TW29



100SE15

Drills

### Jobber Drill Sets

No. of Pieces	Brand	Material	Coating/Finish	Point Angle	Description	EDP No.
<b>400N/440N/480N Series Nitro® Heavy-Duty Jobber Drill Sets</b>						
13	Nitro®	High Speed Steel	Black & Gold	135°	1/16" - 1/4" BY 64ths	400N13
15	Nitro®	High Speed Steel	Black & Gold	135°	1/16" - 1/2" BY 32nds	400N15
19	Nitro®	High Speed Steel	Black & Gold	135°	Maintenance Set - 1/16, 5/64, 3/32, 1/8, #29, #25, 5/32, #21, 3/16, #7, 7/32, 1/4, F, 5/16, U, 3/8, 27/64, 7/16, 1/2	400N19
21	Nitro®	High Speed Steel	Black & Gold	135°	1/16" - 3/8" BY 64ths	400N21
21	Nitro®	High Speed Steel	Black & Gold	135°	1/16" - 1/4" BY 64ths & 9/32" - 1/2" BY 32nds	400N21V
26	Nitro®	High Speed Steel	Black & Gold	135°	A - Z	400N26
29	Nitro®	High Speed Steel	Black & Gold	135°	1/16" - 1/2" BY 64ths	400N29
29	Nitro®	High Speed Steel	Black & Gold	135°	DRILL PAL 1/16" - 1/2" BY 64ths	400NW29
60	Nitro®	High Speed Steel	Black & Gold	135°	#1 - #60	400N60
115	Nitro®	High Speed Steel	Black & Gold	135°	1/16" - 1/2" BY 64ths, #1 - 60, A - Z	400N0115
<b>450T Series Jobber Drill Sets</b>						
13		High Speed Steel	TiN Tipped	135°	1/16" - 1/4" BY 64ths	450T13
15		High Speed Steel	TiN Tipped	135°	1/16" - 1/2" BY 32nds	450T15
21		High Speed Steel	TiN Tipped	135°	1/16" - 3/8" BY 64ths	450T21
29		High Speed Steel	TiN Tipped	135°	1/16" - 1/2" BY 64ths	450T29
29		High Speed Steel	TiN Tipped	135°	DRILL PAL 1/16" - 1/2" BY 64ths	450TW29
60		High Speed Steel	TiN Tipped	135°	#1 - 60	450T60
<b>100SE Series Jobber Drill Sets</b>						
13		High Speed Steel	Black Oxide	118°	1/16" - 1/4" BY 64ths	100SE13
15		High Speed Steel	Black Oxide	118°	1/16" - 1/2" BY 32nds	100SE15
21		High Speed Steel	Black Oxide	118°	1/16" - 3/8" BY 64ths	100SE21
21		High Speed Steel	Black Oxide	118°	1/16" - 1/4" BY 64ths & 9/32" - 1/2" BY 32nds	100SE21V
29		High Speed Steel	Black Oxide	118°	DRILL PAL 1/16" - 1/2" BY 64ths	100SEW29
29		High Speed Steel	Black Oxide	118°	1/16" - 1/2" BY 64ths	100SE29



## Jobber Drill Sets



200B29

### Jobber Drill Sets

No. of Pieces	Brand	Material	Coating/Finish	Point Angle	Description	EDP No.
<b>200/240/280 Series Jobber Drill Sets</b>						
13	USA	High Speed Steel	Black Oxide	118°	1/16" - 1/4" BY 64ths	200A13
15	USA	High Speed Steel	Black Oxide	118°	1/16" - 1/2" BY 32nds	200A15
19	USA	High Speed Steel	Black Oxide	118°	Maintenance Set - 1/16, 5/64, 3/32, 1/8, #29, #25, 5/32, #21, 3/16, #7, 7/32, 1/4, F, 5/16, U, 3/8, 27/64, 7/16, 1/2	200A19
20	USA	High Speed Steel	Black Oxide	118°	#61 - #80	200A20
21	USA	High Speed Steel	Black Oxide	118°	1/16" - 3/8" BY 64ths	200A21
21	USA	High Speed Steel	Black Oxide	118°	1/16" - 1/4" BY 64ths & 9/32" - 1/2" BY 32nds	200A21V
26	USA	High Speed Steel	Black Oxide	118°	A - Z	200A26
29	USA	High Speed Steel	Black Oxide	118°	1/16" - 1/2" BY 64ths	200A29
29	USA	High Speed Steel	Black Oxide	118°	DRILL PAL 1/16" - 1/2" BY 64ths	200AW29
60	USA	High Speed Steel	Black Oxide	118°	#1 - #60	200A60
115	USA	High Speed Steel	Black Oxide	118°	1/16" - 1/2" BY 64ths, #1 - 60, A - Z	200A0115
<b>200B/240B/280B Series Jobber Drill Sets</b>						
13	USA	High Speed Steel	Bright	118°	1/16" - 1/4" BY 64ths	200B13
15	USA	High Speed Steel	Bright	118°	1/16" - 1/2" BY 32nds	200B15
19	USA	High Speed Steel	Bright	118°	Maintenance Set - 1/16, 5/64, 3/32, 1/8, #29, #25, 5/32, #21, 3/16, #7, 7/32, 1/4, F, 5/16, U, 3/8, 27/64, 7/16, 1/2	200B19
21	USA	High Speed Steel	Bright	118°	1/16" - 3/8" BY 64ths	200B21
21	USA	High Speed Steel	Bright	118°	1/16" - 1/4" BY 64ths & 9/32" - 1/2" BY 32nds	200B21V
26	USA	High Speed Steel	Bright	118°	A - Z	200B26
29	USA	High Speed Steel	Bright	118°	1/16" - 1/2" BY 64ths	200B29
60	USA	High Speed Steel	Bright	118°	#1 - #60	200B60
115	USA	High Speed Steel	Bright	118°	1/16" - 1/2" BY 64ths, #1 - 60, A - Z	200B0115

## Jobber Drill Sets




400HD21

Drills

Jobber Drill Sets						
No. of Pieces	Brand	Material	Coating/Finish	Point Angle	Description	EDP No.
400/440/480 & 400E Series Heavy-Duty Jobber Drill Sets						
13	USA	High Speed Steel	Black Oxide	135°	1/16" - 1/4" BY 64ths	400HD13
15	USA	High Speed Steel	Black Oxide	135°	1/16" - 1/2" BY 32nds	400HD15
19	USA	High Speed Steel	Black Oxide	135°	Maintenance Set - 1/16, 5/64, 3/32, 1/8, #29, #25, 5/32, #21, 3/16, #7, 7/32, 1/4, F, 5/16, U, 3/8, 27/64, 7/16, 1/2	400A19
21	USA	High Speed Steel	Black Oxide	135°	1/16" - 3/8" BY 64ths	400HD21
21	USA	High Speed Steel	Black Oxide	135°	1/16" - 1/4" BY 64ths & 9/32" - 1/2" BY 32nds	400HD21V
26	USA	High Speed Steel	Black Oxide	135°	A - Z	400HD26
29	USA	High Speed Steel	Black Oxide	135°	1/16" - 1/2" BY 64ths	400HD29
29	USA	High Speed Steel	Black Oxide	135°	DRILL PAL 1/16" - 1/2" BY 64ths	400AW29
60	USA	High Speed Steel	Black Oxide	135°	#1 - #60	400HD60
115	USA	High Speed Steel	Black Oxide	135°	1/16" - 1/2" BY 64ths, #1 - 60, A - Z	400HD0115
13		High Speed Steel	Black & Gold	135°	1/16" - 1/4" BY 64ths	400HDE13
15		High Speed Steel	Black & Gold	135°	1/16" - 1/2" BY 32nds	400HDE15
21		High Speed Steel	Black & Gold	135°	1/16" - 3/8" BY 64ths	400HDE21
21		High Speed Steel	Black & Gold	135°	1/16" - 1/4" BY 64ths & 9/32" - 1/2" BY 32nds	400HDE21V
29		High Speed Steel	Black & Gold	135°	1/16" - 1/2" BY 64ths	400HDE29
29		High Speed Steel	Black & Gold	135°	DRILL PAL 1/16" - 1/2" BY 64ths	400EW29

## Jobber Drill Sets



400T




500

### Jobber Drill Sets

No. of Pieces	Brand	Material	Coating/Finish	Point Angle	Description	EDP No.
<b>400T Series Heavy-Duty Jobber Drill Sets</b>						
29	USA	High Speed Steel	TiN	135°	1/16" - 1/2" BY 64ths	400T29
<b>500/540/580 &amp; 500E/580E Series Cobalt Heavy-Duty Jobber Drill Sets</b>						
13	USA	Cobalt	Bronze	135°	1/16" - 1/4" BY 64ths	500A13
15	USA	Cobalt	Bronze	135°	1/16" - 1/2" BY 32nds	500A15
21	USA	Cobalt	Bronze	135°	1/16" - 3/8" BY 64ths	500A21
21	USA	Cobalt	Bronze	135°	1/16" - 1/4" BY 64ths & 9/32" - 1/2" BY 32nds	500A21V
26	USA	Cobalt	Bronze	135°	A - Z	500A26
29	USA	Cobalt	Bronze	135°	1/16" - 1/2" BY 64ths	500A29
29	USA	Cobalt	Bronze	135°	DRILL PAL 1/16" - 1/2" BY 64ths	500AW29
60	USA	Cobalt	Bronze	135°	#1 - #60	500A60
115	USA	Cobalt	Bronze	135°	1/16" - 1/2" BY 64ths, #1 - 60, A - Z	500A0115
13		Cobalt	Bronze	135°	1/16" - 1/4" BY 64ths	500E13
15		Cobalt	Bronze	135°	1/16" - 1/2" BY 32nds	500E15
21		Cobalt	Bronze	135°	1/16" - 3/8" BY 64ths	500E21
21		Cobalt	Bronze	135°	1/16" - 1/4" BY 64ths & 9/32" - 1/2" BY 32nds	500E21V
29		Cobalt	Bronze	135°	1/16" - 1/2" BY 64ths	500E29
60		Cobalt	Bronze	135°	#1 - #60	500E60

## Jobber Drill Sets

Drills



800A13



200LH29

Jobber Drill Sets						
No. of Pieces	Brand	Material	Coating/Finish	Point Angle	Description	EDP No.
<b>800 Series Metric Jobber Drill Sets</b>						
13		High Speed Steel	Black & Gold	135°	1mm - 7mm BY 0.5mm	800A13
19		High Speed Steel	Black & Gold	135°	1mm - 10mm BY 0.5mm	800A19
25		High Speed Steel	Black & Gold	135°	1mm - 13mm BY 0.5mm	800A25
<b>200LH Series Left Hand Jobber Drill Sets</b>						
13	USA	High Speed Steel	Bright	118°	1/16" - 1/4" BY 64ths	200LH13
15	USA	High Speed Steel	Bright	118°	1/16" - 1/2" BY 32nds	200LH15
21	USA	High Speed Steel	Bright	118°	1/16" - 3/8" BY 64ths	200LH21
21	USA	High Speed Steel	Bright	118°	1/16" - 1/4" BY 64ths & 9/32" - 1/2" BY 32nds	200LH21V
29	USA	High Speed Steel	Bright	118°	1/16" - 1/2" BY 64ths	200LH29