



White Super Polish

super polish pad

PRODUCT SPECIFICATIONS

1.0 Description

The White Polish floor maintenance pad is made of polyester fibers in a dense textured, nonwoven pattern, bonded with a sturdy adhesive.

2.0 Properties

Property	Value
Thickness	1 in 26 mm
Weight	24 osy 814 gsm
Fiber Type	Recycled Polyester
Binder System	Cross-linkable water based
Binder Application	Spray
Abrasive Application	N/A
Abrasive	N/A
Color	White
Pack	5 per case*

*27" and 28" also available in 2 per case



Full Cycle® Products are certified by Green Seal™ for Environmental Innovation based on faster biodegradation in landfill conditions and 100% recycled content/natural fiber. Green Seal.org/GS20

Note: Due to the intrinsic properties of the material and variable conditions of use, there may be slight variations in the specifications and results. Please contact Americo with any questions or concerns.

Americo Manufacturing Company, Inc.

1-800-849-6287

www.americomfg.com

©2017

Rev. 06/01/17
White Super Polish Product Specifications

3.0 Use

This extra fine pad has been designed for polishing clean, dry floors. Use dry or with restorative chemicals, to produce a wet look gloss to newly finished floors. For use with standard electric floor machines, ultra high speed machines, orbital scrubbers and automatic scrubbers. Ideal for use on machines speeds up to 3000 rpm.

4.0 Construction

The White Polish Pad is made of 100% recycled polyester fibers and water based resins. This product is made to be reversible.

5.0 Labeling

Labeling is to clearly identify product, size, and quantity. Americo brand or private label is available for this product.

6.0 Environmental Initiatives

- Polyester fiber used in our pads come from 100% post consumer and industrial recycled waste product.
- Full Cycle™**, formulated to biodegrade* in a fraction of the time that it takes conventional floor pads once discarded into an active landfill.
- Water Based Latex Resins are used in the manufacturing process. No phenol-formaldehyde resins are used in our binding process.
- Shipping cartons contain at least 45% recycled material.
- Plant is operating under EPA approved Clean Air Permit.

* For complete details or to view ASTM D5511 test results visit www.AmericoFullCycle.com

7.0 Directions for Use

Dust mop or sweep floors prior to polishing. For use on a clean, dry floor. May be used dry or with restorative chemicals.

8.0 Product Care

To prolong the life of this product it may be washed using a hose with a pressure spray nozzle to remove soil. To dissolve heavy soil or finish this pad may be soaked in detergent or diluted stripping solution prior to washing.

9.0 Sizes

Disc Size (Diameter) (O.D. ± 0.06 inch)	Center Hole
7¾ inch	3.25 inch
9½ inch	3.25 inch
10 inch	3.25 inch
11 inch	3.25 inch
12 inch	3.25 inch
13 inch	3.25 inch
14 inch	3.25 inch
15 inch	3.25 inch
16 inch	3.25 inch
17 inch	3.25 inch
18 inch	3.25 inch
19 inch	3.25 inch
20 inch	3.25 inch
21 inch	3.25 inch
22 inch	3.25 inch
23 inch	3.25 inch
24 inch	3.25 inch
27 inch	3.25 inch
28 inch	3.25 inch

Rectangular Size

12 inch x 18 inch
14 inch x 20 inch
14 inch x 28 inch
14 inch x 32 inch

Additional sizes available.
Check for availability on additional center hole dimensions.