



PN 901226
UPC 7 84090 03865 4

USB-C Portable Dock

Key Features:

- Universal Compatibility for USB-C Systems
- Supports up to 2 external displays via HDMI, DisplayPort or VGA
- 2x SuperSpeed USB 3.0 Ports
- 3x USB-C Ports (Specific Functionality)
- Power Passthrough from USB-C charger (not included)
- Supports up to 100W Power Passthrough

Increase your productivity with our plug and play power passthrough docking station, the VisionTek VT200 USB-C Docking Station for Windows™ and Mac™ laptop systems. With a single USB-C connection, you can connect up to two external displays, transfer files and data at up to 5Gbps speeds and charge mobile devices.

- Universally Compatible USB-C – Windows™ or Mac™, the VT200 is compatible through the single, included USB-C 4 inch cable, making this the ideal docking station for mixed system environments.
- USB-C Pass-Through Power – Plug your laptop's USB-C power adapter into the dock's USB-C Power-In port on the side to provide passthrough power, up to 100W, depending on system and charger being used. The VT200 can also be used without the power adapter to charge your mobile devices from the laptop's battery.
- Connect Up to Two External Displays in HD – The VT200 has three video ports to provide video connection options that suit your needs using MST technology. Use 1 DisplayPort, 1 HDMI, or 1 VGA together for a multi-display experience. Three external displays requires disabling the system screen and specialized display settings, see manual. (Windows™ systems support up to two external displays. Mac™ systems support one extended and one cloned/mirrored external display.)
- Expanded Selection of Ports – Flexibility and portability are the goals with the VT200, by offering some of the most commonly needed ports in one dock using the included 4 inch USB-C cable.
 - 1x HDMI, 1x DP and 1x VGA port let's you connect external displays to increase your system workspace.
 - 2x USB 3.0 ports let you connect external storage, full size keyboard and mouse, or mobile devices.
 - 3x USB-C ports total (1x USB-C for optional user supplied Power Delivery, 1x USB-C for additional devices).
 - Removable 4 inch USB-C cable to connect to your sytem USB-C port.



Part Number: 901226 | UPC Code: 7 84090 03865 4

Front



USB-C Cable
Storage

Sides



USB-C
Power
Passthrough
to System
Port



USB-C
Data
Transfer
Port

USB-C
Power-In
Port
(charger not
included)

Back



VGA
Port

HDMI
Port

DisplayPort
Port

USB 3.0
Ports

Part Number: 901226 | UPC Code: 7 84090 03865 4

Dock
Specifications

System Requirements

Operating Systems Supported	Windows™ 7, 8, 8.1, 10 - MacOS™ 10.X and later
System Resource Requirement	System must support Power Delivery mode through USB-C DP Alt Mode. System must support MST compatibility for multi-display setup.
USB-C Power Delivery	Supports USB-C PD 3.0 5V/9V/12V/15V/20V up to 3A 100W Maximum

Dock to System Connection

Dock Connector	USB-C
----------------	-------

Video Connections

Single Display	DisplayPort: Up to 3840 x 2160 @30Hz HDMI Port: Up to 1920 x 1080 @60Hz VGA Port: Up to 1920 x 1080 @60Hz
Dual Display	DP + HDMI: Up to 1920 x 1080 @60Hz DP + VGA: Up to 1920 x 1080 @60Hz HDMI + VGA: Up to 1920 x 1080 @60Hz
Triple Display	DP + HDMI + VGA: Up to 1280 x 720 @60Hz

* Windows™ systems support up to three external displays.
** Mac™ systems support one extended and one cloned/mirrored external display.

USB Connections

Side 1	1x USB-C Power Delivery Input Port
Side 2	1x USB-C Power Passthrough Output Port 1x USB-C Data Transfer Port up to 5Gbps
Back	2x USB 3.0 Type-A Port

Power and Environmental

Power	Power delivery compatible with user supplied USB-C Power Adapter up to 100W. No power adapter included. *Aftermarket USB-C Charging Compatible.
Operating Temperature	0 to 40° C (32 to 104° F)
Storage Temperature	-10 to 70° C (-14 to 158° F)
Relative Humidity	10% to 90% non-condensing

Product Dimensions

Product Dimensions	Length: 5" (127mm) Depth: 2.5" (64mm) Height: 0.6" (14mm)
Product Weight	3.3oz (94g)
Included Cable Length	4" (102mm)
Product Color and Material	Black ABS

Packaging Dimensions

Packaging Style	Retail Box
Packaging Specifications	Length: 7.38" (188mm) Depth: 5.38" (137mm) Height: 1" (25mm) Weight: 5.8oz (165g)
Master Carton	40 pcs
Individual Package Contents	1x VT200 Dock 1x USB-C to USB-C Cable 4" (102mm) 1x Quick Start Manual

Country of Origin and Warranty Information

Country of Origin	China
Certifications and Compliance	CE, FCC, SGS, REACH and RoHS
Warranty	2-Years Limited

Compatible Recommendations

Power Supply Options	VisionTek USB-C 90W Charger - PN 901285 Dell Adapter 90W Type-C - PN 492-BCBK
Cable Options	VisionTek DP to DP 2M Cable - PN 901211 VisionTek HDMI Pivot 10ft Cable - PN 900750 VisionTek USB-C 100W PD 1M Cable - PN 901269
External Storage Options	VisionTek 1TB XT USB 3.0 Pocket SSD - PN 901241