


Charging Unit

Clamp-On Desktop Charging Unit: KBEP-CGR*



Features:

- Adjustable clamp is compatible with common desk and tabletop surfaces
- Includes AC outlet, USB-A port, and USB-C PD port
- Conveniently charges Chromebooks, laptops, tablets, and smart phones


Technical Specifications:

AC Outlet	100V-120V, 60Hz, modified sine wave, 100W continuous output power, 120W peak output power (10 minutes)
USB-A Port	5V/2.4A (12W)
USB-C PD Port	5V/2A (10W), 12V/1.5A (18W)
Dimensions	8.3\" D (10.3\" with battery inserted*) x 4.9\" W x 5.2\" to 6\" H (based on clamp setting)
Clamp Capacity	0.7\" to 1.5\"

*Battery sold separately

Battery

Rechargeable Battery: KBEP-BAT



Features:


- Easily interchangeable
- Recharges using EdgePower Base
- Charging Station (sold separately)
- Includes LED charge indicator lights

Technical Specifications:

Battery Capacity	146.52 Wh (18 cells)
Cell Type	18650 Li-ion battery (2,200mAh at 3.7V)
Life Cycles	500 times (higher than 80% of the initial capacity)
Shelf Life	1 year after first charge
Battery Shipping Classifications	UN 3480
Dimensions	9.1\" D x 3.0\" W x 2.1\" H
Battery Weight	2.75 lbs.
Battery Cell Recharge Time	2 hours

Base Charging Stations

Single Battery Charger: KBEP-BASE1




Features:

- Charges and stores EdgePower batteries
- IEC plug with 6.5' power cord (3 and 9-bay only)
- Available in Single, 3-bay, and 9-bay configurations
- Fully recharges battery banks in 2 hours
- 3-bay is stackable and expandable
- 3-bay and 9-bay units offer a Kensington Security Slot for theft deterrence


Dimensions:

Single Battery Charger	0.75\" D x 3.25\" W x 2.25\" H
3-Bay Base Charging Station	12\" D x 15\" W x 6\" H
9-Bay Base Charging Station	12\" D x 15\" W x 13.5\" H

3-Bay Base Charging Station: KBEP-BASE3



9-Bay Base Charging Station: KBEP-BASE9



Additional Technical Features:

Device Protection:

- Temperature Protection
- Short Circuit Protection
- Self-Balancing Algorithm
- Overcharge Protection

Output Protection:

- AC/USB Outlet Protection
- Power Overflow Protection
- Voltage Underflow/Overflow Protection

Input Protection:

- Charging Overflow Protection
- Charging Circuit Protection

Warranty: Limited one (1) year from date of shipment

Operating Temperatures:
Charging 32 to 113F (0 to 45C)
Discharge 14 to 131F (-10 to 55 C)



Certifications:

	FCC	Prop 65	CPSC	UL	cULus	CSA	cETLus
Battery	•	•	•				•
Clamp	•	•	•				
3 & 9 Bay Chargers	•	•		•		•	
Single Charger	•	•			•		

kwikboost

EDGEPOWER™

The Cordless Power Solution for Today's Classroom



LUXOR

SALES: 800-323-4656 | FAX: 847-244-1818
LUXORFURN.COM/EDGEPOWER




Kwikboost EdgePower™: Convenient Cordless Charging of Mobile Devices

Every teacher has been there; students show up to class with depleted device batteries. Up until now, the students have either had to share screens with classmates, spend 10 minutes getting loaners from the front office, or the teacher was forced to run unsightly extension cords to the desks, creating a trip hazard.

The Kwikboost EdgePower – an innovative new battery-powered charging station that easily clamps onto the edge of desks, tables, and other common classroom surfaces - makes this problem a thing of the past by providing a neat, clean, 100% cord-free way for students to charge virtually any electronic device at their desk or table.



POWERFUL | RECHARGEABLE | PORTABLE



Benefits:

- Eliminates trip hazards
- Neat, clean appearance
- Fast, plug-n-play operation
- Moves with desk when reconfiguring a room for seamless transitions
- Cost effective
- Easy installation

Charging Capabilities:

- Charges a typical laptop up to 2 times
- Charges a typical tablet up to 4 times
- Charges a typical Chromebook up to 4 times
- Charges a typical smart phone up to 14 times