

### TECHNICAL DATA



R1050



R1200



R1210



R1100



R1110



R1120

#### Model R1050 Test Lead Set

- Right angle and straight end leads with shrouded banana plugs
- Compatible with all instruments, test probes and clips that accept 0.16" (4mm) diameter shrouded banana connectors
- Lead length: 48" (1.2m)
- Cat. III 1000V safety rating
- 10A Maximum

#### Model R1200 Plunger Style Alligator Clip Set

- Spring loaded alligator clips with 0.7" (17mm) jaw opening
- Insulated jaws
- Recommended for use with REED R1050 Test Lead Set
- CAT III. 1000V safety rating
- 10A Maximum

#### Model R1100 Test Probe Set, Banana Style

- Banana-style spring contacts
- Probe tip length: 0.8" (19mm)
- Probe length: 4.1" (105mm)
- Cat. III 1000V safety ratings
- Recommended for use with REED R1050 Test Lead Set
- 10A Maximum
- Includes protective tip caps

#### Model R1210 Alligator Clip Set, Large

- Dimensions: Length: 3.9" (99mm), Jaw: 1" (26mm)
- 1000V, 10A
- CAT III. 1000V and CAT IV. 600V

#### Model R1110 Test Probe Set, Sharp Point

- Sharp points for piercing insulation
- Stainless steel tips
- Probe tip length: 0.6" (16mm)
- Probe length: 3.9" (100mm)
- 1000V, 10A
- Cat. II 1000V, Cat. III 1000V and Cat. IV 600V safety ratings
- Compatible with test leads that accept 0.16" (4mm) diameter shrouded banana connectors
- 10A Maximum
- Includes protective tip caps

#### Model R1120 Safety Test Probe Set, Sharp Point


- Sharp points for piercing insulation
- Stainless Steel Tips
- Ergonomic grip
- Dimensions: Length: 5.6" (142mm), Tip: 0.2" (4mm)
- 1000V, 10A
- CAT III. 1000V and CAT IV. 600V
- CE certified
- Includes protective tip caps

*Continued...*


### TECHNICAL DATA



R1130



R1140



R1000



R1220

#### Model R1130 Test Probe Set, Banana Style

- Banana-style spring contacts
- Dimensions: Length: 4.7" (120mm), Tip: 0.8" (19mm)
- 1000V, 10A
- CAT III. 1000V, CAT IV. 600V
- CE certified
- Includes protective caps

#### Model R1000 Safety Test Lead Set

- Compatible with all instruments, test probes and clips that accept 0.16" (4mm) diameter shrouded banana connectors
- Stainless steel tips
- Lead length: 48" (1.2m)
- Probe tip length: 0.2" (5mm)
- Probe tip diameter: 0.08" (2mm)
- Cat. II 1000V, Cat. III 1000V and Cat. IV 600V safety ratings
- 10A Maximum

#### Model R1140 Electronic Test Probe Set, Sharp Point

- Sharp point and long probe designed for electronic testing
- Dimensions: Length: 4.5" (113mm), Tip: 0.2" (4mm)
- CAT II. 1000V

#### Model R1220 Alligator Clip Set

- Dimensions: Jaw: 0.4" (11mm)
- Insulated with flexible boots
- Accepts standard 4mm diameter test leads
- 1000V, 10A
- CAT III. 1000V
- CE certified

*Continued...*



R1020



R1020-FUSE

### Model R1020 Fused Test Lead Set

- Sharp points for piercing insulation
- Built-in fuses for added protection
- Stainless steel tips
- Ergonomic comfort grip
- Dimensions: Length: 48" (1.2m) Tip Length: 0.2" (4mm) Probe Length: 5.4" (137mm)
- 1000V, 10A
- CAT III. 1000V and CAT IV. 600V
- CE certified

### Model R1020-FUSE Replacement Fuses

- Replacement fuses for use with the R1020

### Model R1000-KIT Safety Test Lead and Alligator Clips Kit

- Includes:
- R1000 Safety Test Lead Set
  - R1220 Alligator Clip Set



### Model R1050-KIT Safety Test Lead Kit

- Includes:
- R1050 Test Lead Set
  - R1210 Alligator Clip Set, Large
  - R1110 Test Probe Set, Sharp Point
  - CA-52A Soft Carrying Case



## TECHNICAL DATA



R1050-KIT2

### Model R1050-KIT2

#### Deluxe Safety Test Lead Kit

Includes:

- R1050 Test Lead Set
- R1220 Alligator Clip Set
- R1210 Alligator Clip Set, Large
- R1140 Electronic Test Probe Set, Sharp Point
- R1100 Test Probe Set, Banana Style
- R1110 Test Probe Set, Sharp Point
- R1120 Safety Test Probe Set, Sharp Point
- R1130 Test Probe Set, Banana Style
- R1000 Safety Test Lead Set
- R1200 Plunger Style Alligator Clip Set
- CA-05A Soft Carrying Case

Model	Description
R1050	Test Lead Set
R1210	Alligator Clip Set, Large
R1200	Plunger Style Alligator Clip Set
R1100	Test Probe Set, Banana Style
R1110	Test Probe Set, Sharp Point
R1120	Safety Test Probe Set, Sharp Point
R1130	Test Probe Set, Banana Style
R1140	Electronic Test Probe Set, Sharp Point
R1000	Safety Test Lead Set
R1220	Alligator Clip Set
R1000-KIT	Safety Test Leads with Alligator Clips
R1020	Fused Test Lead Set
R1020-FUSE	Replacement Fuses
R1050-KIT	Safety Test Lead Kit
R1050-KIT2	Deluxe Safety Test Lead Kit