



Main

| | |
|------------------------------------|--|
| Range | TeSys |
| Device short name | GS2AE |
| Product or component type | Shaft extension |
| Accessory / separate part category | Control accessory |
| Range compatibility | TeSys GS GS2F TeSys GS GS2G TeSys GS GS2J TeSys GS GS2K TeSys GS GS2L TeSys GS GS2M TeSys GS GS2N TeSys GS GS2P TeSys GS GS2Q FuPacT GS GSC50 FuPacT GS GSB63 FuPacT GS GSD63 FuPacT GS GSB100 FuPacT GS GSC125 FuPacT GS GSD125 FuPacT GS GSD160 FuPacT GS GSB200 FuPacT GS GSB250 FuPacT GS GSD250 FuPacT GS GSB400 FuPacT GS GSD400 |
| Switch rated current | 50 A 60 A 63 A 100 A 125 A 160 A 200 A 250 A 315 A 400 A |

Complementary

| | |
|---------------------|-----------------------|
| Length | 12.60 in (320 mm) |
| Shaft cross section | 10 x 10 mm |
| Net Weight | 0.62 lb(US) (0.28 kg) |

Ordering and shipping details

| | |
|-----------------------|--------------------------------|
| Category | 22640 - IEC DISCONNECT-GS1,LK3 |
| Discount Schedule | I11 |
| GTIN | 00785901126911 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.55 lb(US) (0.25 kg) |
| Returnability | Yes |
| Country of origin | TN |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 0.87 in (2.2 cm) |
| Package 1 width | 4.61 in (11.7 cm) |
| Package 1 Length | 17.01 in (43.2 cm) |
| Unit Type of Package 2 | BAG |
| Number of Units in Package 2 | 1 |
| Package 2 Weight | 8.96 oz (254 g) |
| Package 2 Height | 0.87 in (2.2 cm) |
| Package 2 width | 4.61 in (11.7 cm) |
| Package 2 Length | 17.01 in (43.2 cm) |
| Unit Type of Package 3 | S02 |
| Number of Units in Package 3 | 20 |
| Package 3 Weight | 11.89 lb(US) (5.393 kg) |
| Package 3 Height | 5.91 in (15 cm) |
| Package 3 width | 11.81 in (30 cm) |
| Package 3 Length | 15.75 in (40 cm) |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|