



Fuselage™

Full Frame Safety Glasses with Black Frame, Foam Padding, Clear Lens and Anti-Scratch / Anti-Fog Coating

- Flame resistant soft foam padding forms a seal to keep out dust and airborne particles
- Comes with both temples AND elastic headband strap
- Temples and strap snap in or out...easily converts from a safety glass to a dust goggle and back
- Bayonet nylon temples with rubber tips for a secure fit
- Molded nose bridge design to fit the vast majority of users
- 8 Base curve lens
- Meets ANSI Z87.1+
- **⚠️ WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Dusty Work Areas
- General Manufacturing
- Construction Applications
- Indoor Work



Technical Data

Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	72 Pair/Case
Case Dimensions (in)	19.29 x 11.81 x 10.63
Case Weight (lbs)	13.89
Country of Origin	Taiwan
Lens	Clear
Frame Style	Foam-Lined
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Anti-Scratch, Anti-Fog
Bridge	Rubber
Temple	Bayonet, Rubber Tips
Diopter	--
Base Curve	8
Construction	--
Certifications	ANSI Z87.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Care Instructions

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-13



SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS COATING	UPC	UPC (INNER)	UPC (CASE)
250-50-0420	Black	Clear	Clear	AS/AF	616314062414	01616314062413	02616314062412
250-50-0421	Black	Tinted	Gray	AS/AF	616314062421	01616314062420	02616314062429
250-50-0422	Black	I/O	Clear	AS/AF	616314153310	01616314153319	02616314153318
250-50-0425	Black	Mirror	Silver	AS/AF	616314156564	01616314156563	02616314156562
250-50-0426	Black	Mirror	Blue	AS/AF	616314156571	01616314156570	02616314156579
250-50-0429	Black	Tinted	Amber	AS/AF	616314062438	01616314062437	02616314062436
250-50-0520	Black	Clear	Clear	AS/FL360	616314209543	01616314209542	02616314209541
250-50-0521	Black	Tinted	Gray	AS/FL360	616314209550	01616314209559	02616314209558

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated