



Spitfire® RTU & SC

21

Power Cleaner

Spray-and-wipe cleaner that removes the toughest dirt, grime, oils and stains from a wide variety of surfaces.

Features & Benefits

- Heavy duty formula removes toughest grease, oil, tire marks, ink, graffiti, and heel marks without leaving residue or streaks behind
- Conveniently available in Ready-to-Use
- Premium performance, solvent based surface cleaner
- Red in color with fresh pine scent
- Small job convenience, portability, less flammable than aerosols

Applications

- Spray & wipe cleaner for hard surfaces
- Use to remove marker and paint
- Cleaner/Degreaser for shops and kitchens NSF C-1





Spitfire® RTU & SC

Power Cleaner

Use instructions

- Spray on hard surfaces to be cleaned.
- Allow power cleaner to penetrate and lift soils.
- Wipe with a clean cloth.
- Does not require a water rinse after use.
- Do not use on glass, aluminum or water-based paint.
- Suitable for use in areas where food or packaging will not come in contact with spray or surface during or after the use of this product.

| Technical data | Spitfire® RTU | Spitfire® SC |
|----------------|-------------------|---|
| Certifications | NFS, Kosher | NFS, Kosher |
| Color/Form | Clear red, liquid | Red, liquid |
| pH | 12.3 | 13.6 (Concentrate) 12.22 (Use Dilution 1:16) |
| Scent | Fresh pine | Fresh pine |
| Shelf Life | 2 Years | 2 Years |

| Product | Pack size | Dilution | Product code | |
|--------------------|---|--------------|--------------|--|
| Spitfire® RTU & SC | 12 x 32 oz./946 mL Spray Bottles (with 2 sprayers) - SC | Ready-to-use | 95891789 | |
| Spitfire® RTU & SC | 2 x 84.5 oz./2.5 L J-Fill® - SC | 1:16 | 95892221 | |
| Spitfire® RTU & SC | 2 x 50.7 oz./1.5 L RTD® - SC | 1:16 | 95891201 | |
| Spitfire® RTU & SC | 1 x 1.32 gal./5 L RTD® - SC | 1:16 | 95892546 | |
| Spitfire® RTU & SC | 12 x 32 oz./946 mL Spray Bottles (with 2 sprayers) | | D903919 | |
| Spitfire® RTU & SC | 4 x 1 gal./3.78 L Containers | Ready-to-use | 100870948 | |
| Spitfire® RTU & SC | 2 x 1.5 gal./5.68 L Command Center™/MC | 1:16 | 100969925 | |

Safe handling

Please make sure your employees read and understand the product label and Safety Data Sheet before using this product. The label contains directions for use; and both the label and SDS contain hazard warnings, precautionary statements and first aid procedures. SDS are available online at www.diversey.com or by calling 888.352.2249. Improper use or dilution may result in damage to surfaces and may result in health and physical hazards that match those of the concentrate. Please refer to the Diversey HazMat Library, only available through Internet Explorer, <http://naextranet.diversey.com/dot/>, for up-to-date shipping information.