



# BLACKWIRE 3200 SERIES

For faster UC deployments.

Flexibility you need—at a price you can afford.

Value and flexibility

# BLACKWIRE 3200 SERIES

## KEY FEATURES



- A** Leatherette ear cushions fold flat for easy storage (C3215/C3225)
- B** Call answer/end, mute, volume +/-
- C** Variants include universal USB or USB-C type connectivity
- D** 3.5 mm connectivity lets you work on a variety of mobile devices (C3215/C3225)

## BLACKWIRE 3210/3215 (MONAURAL)



## BLACKWIRE 3220/3225 (STEREO)



## INCLUDED ACCESSORIES

- Carrying case for easy storage and portability (C3215/C3225)

The Blackwire 3200 Series corded UC headsets are durable, lightweight, easy to deploy and come in a variety of connectivity and wearing options. Add insights from Plantronics Manager Pro, an additional service, and you've got a future proof solution. The Blackwire 3200 series with Plantronics signature audio provides top notch features at a price you can afford.

## TOP FEATURES

- Available in monaural (C3210/C3215) or hi-fi stereo with passive noise reduction (C3220/C3225)
- Variants include universal USB or USB-C
- Connectivity to smartphone and tablet via 3.5 mm (C3215/C3225)
- Intuitive inline controls to answer/end calls, control volume, and mute
- PC wideband audio with noise-canceling microphones for high-quality PC telephony
- Plantronics Manager Pro, an additional purchase, enables your IT team to gain insight into every compatible Plantronics headset being used company-wide

## SPECIFICATIONS

Connects to	PC via USB/USB-C, connects to mobile devices and tablets via 3.5 mm and devices that support USB-C
Compatible with	Windows® or Mac OS
Ideal for	Users transitioning to PC telephony for webinars, conference calls, music, and other multimedia applications
PC audio performance	Dynamic EQ, microphone frequency response 100 Hz–10 kHz optimal for PC wideband voice telephony (up to 6,800 Hz), hi-fi stereo (C3220/C3225). Receive output from 20 Hz–20 kHz, enhanced digital signal processing (DSP), noise-canceling microphone, adjustable audio alerts with Plantronics Hub software (mute/volume)*
Hearing protection	SoundGuard: Acoustic limiting for protection against sounds above 118 dBA
Remote call control	Call answer/ignore/end/hold, redial, mute, volume +/-
Models	<b>C3210 USB</b> (Monaural); <b>C3210 USB-C</b> (Monaural); <b>C3215 USB</b> (Monaural with 3.5 mm); <b>C3215 USB-C</b> (Monaural with 3.5 mm); <b>C3220 USB</b> (Stereo); <b>C3220 USB-C</b> (Stereo); <b>C3225 USB</b> (Stereo with 3.5 mm); <b>C3225 USB-C</b> (Stereo with 3.5 mm); Built for UC applications and softphones from Avaya®, Cisco®, Microsoft® and more*. Certified for Skype for Business

Weights	Total weight		Headset top		Bottom cable to USB-A		Bottom cable to USB-C	
	Grams	Lbs/oz	Grams	Lbs/oz	Grams	Lbs/oz	Grams	Lbs/oz
<b>Blackwire 3210</b>	87	0.192	–	–	–	–	–	–
<b>Blackwire 3215</b>	96	0.212	64	0.141	32	0.071	32	0.071
<b>Blackwire 3220</b>	118	0.26	–	–	–	–	–	–
<b>Blackwire 3225</b>	121	0.267	92	0.203	29	0.064	29	0.064

\*Download the latest release of Plantronics Hub software to get one-touch call answer/end with these softphones.

For more information about the Blackwire 3200 Series or other Plantronics products, please visit our website at [plantronics.com](http://plantronics.com).

## GLOBAL CUSTOMER CARE

Backed by Plantronics industry-leading global service and support.