

Product Use in your Country or Municipality

Standards that govern use of this product vary by country and sometimes municipality. In the United States, this product is not for use in the Patient Care Vicinity, as defined in the National Electric Code (NEC). This product is approved to CSA C22.2/CuL standards and approved for use in Canada. For application guidance and product selection in your country, please consult a [Tripp Lite Healthcare Product Specialist](#) or your own expert.

Safe-IT Medical-Grade Power Strip, UL 1363, 6x Hospital-Grade Outlets, Antimicrobial, 1.5 ft. (0.45 m) Cord

MODEL NUMBER: **PS-602-HG**



Medical-grade power strip with patented antimicrobial coating and 1.5 ft. cord provides safe, versatile power distribution.

Features

Power Distribution Outside of Patient-Care Vicinities Ideal for use in administrative areas and resident rooms with no line-operated electrical equipment for diagnostic, treatment or monitoring purposes 120V, 50/60 Hz power strip complies with UL 1363 specifications

Exclusive, Patented Antimicrobial Protection Silver ionic powder coating is 99.9% effective in inhibiting the growth of bacteria Patented coating helps to reduce the risk of healthcare-acquired infections (HAIs) in hospitals and other medical environments Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products

Versatile Medical-Grade Solution 6 NEMA 5-15R-HG hospital-grade outlets provide consistent power Rugged, all-metal housing for long life in demanding environments

Premium Safety Features Resettable 15A circuit breaker protects against dangerous overloads Switchless design prevents accidental shut-off

Ready to Use Right Out of the Box Built-in keyhole mounting tabs and flanges make the PS-602-HG easy to install on a variety of surfaces

Highlights

- Patented antimicrobial coating is 99.9% effective in inhibiting the growth of bacteria
- Complies with UL 1363 specifications
- 1.5 ft. cord with NEMA 5-15P-HG hospital-grade plug
- Features 6 NEMA 5-15R-HG hospital-grade outlets

Package Includes

- PS-602-HG UL 1363 Medical-Grade Power Strip with six 15A Hospital-Grade Outlets and 1.5 ft. Cord
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332121042



INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Plug Features	Hospital Grade Plug
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	1.5
Input Cord Length (m)	0.46
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15 amp circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Color	White
Antimicrobial Coating	Yes
Color (AC Line Cord)	White
Included Mounting Accessories	Keyhole mounting tabs and flanges
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole slots = 261.92mm; Distance between end tabs = 330.17mm
Material of Construction	Metal
Outlets Measurement (Center to Center)	38.7mm
Receptacle Color	White
Shipping Dimensions (hwd / cm)	36.20 x 14.60 x 5.08
Shipping Dimensions (hwd / in.)	14.25 x 5.75 x 2.00



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	1.41
Shipping Weight (lbs.)	3.10
Unit Dimensions (hwd / cm)	3.8 x 34.9 x 6.4
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5
Unit Weight (kg)	0.91
Unit Weight (lbs.)	2.00
SPECIAL FEATURES	
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Canada	cUL (Series Number: AGIB12015SL)
UL1363 (Power Tap)	UL1363 (Series Number: AGIB12015SL)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>