

## USB 3.0 SuperSpeed Keystone Jack Type-A Extension Cable (M/F), 3 ft. (0.91 m)

MODEL NUMBER: U324-003-KJ



Adds a USB 3.0 Type-A female port to a universal keystone wallplate, outlet box or panel. Ideal for giving your conference room a professional, clutter-free look.

### Features

#### Mount a USB 3.0 Type-A Port in a Fixed Location

- USB-A female keystone jack connector snaps easily into universal keystone wallplate, outlet box or panel
- Gives your conference room a professional, clutter-free look
- Connects computers, keyboards, external hard drives, flash drives and other USB-A devices
- Data transfer rates up to 5 Gbps
- Bi-directional data interface allows data to flow both directions
- Backward compatible with earlier USB generations

#### Premium Construction for Superior Signal Transfer

- Premium foil and braid shielding for error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors and gold-plated copper contacts
- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Rugged PVC jacket

## Specifications

OVERVIEW	
UPC Code	037332192424

### Highlights

- Connects two USB-A devices, such as computers and flash drives
- Data transfer rates up to 5 Gbps
- Data flows both directions simultaneously
- Twisted 28/24 data/power lines
- Backward compatible with earlier USB generations

### Package Includes

- U324-003-KJ USB 3.0 SuperSpeed Keystone Jack Type-A Extension Cable (M/F), 3 ft.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Technology	USB 3.0 (SuperSpeed); USB
<b>PHYSICAL</b>	
Color	Black; Blue
Cable Length (ft.)	3
Cable Length (m)	0.9
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.06
Shipping Weight (lbs.)	0.13
<b>CONNECTIONS</b>	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (FEMALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>