

# JACKSON\*

SAFETY Brand

## JACKSON SAFETY\* Nemesis\* Safety Glasses

Codes: 25676, 25679, 25659, 22476, 25685, 19642, 25688, 22475, 25692, 14481, 25671, 19639, 22608, 22610, 19644, 22609, 22611, 47384, 47387, 47388, 47383, 47378

### Product Information

Code	Former Code	Lens	Frame	%VLT	Quantity
25676	3000354	Clear	Black	87 – 93	1 each/bag; 12 bags/case
25679	3000355	Clear, Anti Fog	Black	87 – 93	1 each/bag; 12 bags/case
25659	3000359	Amber	Black	85 – 88	1 each/bag; 12 bags/case
22476	3020122	Amber, Anti Fog	Black	82 – 88	1 each/bag; 12 bags/case
25685	3000357	Indoor/Outdoor	Black	45 - 55	1 each/bag; 12 bags/case
19642	3011374	Copper Blueshield	Black	34 – 40	1 each/bag; 12 bags/case
25688	3000356	Smoke, Mirror	Black	8.5 – 13	1 each/bag; 12 bags/case
22475	3020121	Smoke, Anti Fog	Black	8.8 - 15	1 each/bag; 12 bags/case
25692	3004762	IRUV 3.0	Black	8.5 – 18	1 each/bag; 12 bags/case
14481	3000358	Blue, Mirror	Black	4.5 - 8.5	1 each/bag; 12 bags/case
25671	3004761	IRUV 5.0	Black	1.18 – 3.16	1 each/bag; 12 bags/case
19639	3011373	Light Blue	Black	67 – 70	1 each/bag; 12 bags/case
22608	3020706	Clear Anti Fog	Camo	86 – 92	1 each/bag; 12 bags/case
22610	3020708	Amber Anti Fog	Camo	82 – 88	1 each/bag; 12 bags/case
19644	3011375	Bronze	Camo	20 – 26	1 each/bag; 12 bags/case
22609	3020707	Smoke Anti Fog	Camo	8.5 – 15	1 each/bag; 12 bags/case
22611	3020709	Smoke	Red	8.5 – 15	1 each/bag; 12 bags/case
47384	N/A	Clear, Anti Fog	Metallic Blue	87 – 93	1 each/bag; 12 bags/case
47387	N/A	Smoke, Anti Fog	Metallic Blue	8.8 – 15	1 each/bag; 12 bags/case
47388	N/A	Clear, Anti Fog	Silver	87 – 93	1 each/bag; 12 bags/case
47383	N/A	Smoke, Anti Fog	Silver	8.8 – 15	1 each/bag; 12 bags/case
47378	N/A	Clear, Anti Fog	Red	87 – 93	1 each/bag; 12 bags/case



Property	Description
Standards	<ul style="list-style-type: none"> <li>Meets ANSI Z87.1+2015 standards for high impact</li> </ul>
Protection	<ul style="list-style-type: none"> <li>Impact</li> <li>99.9% UVA/UVB/UVC protection</li> <li>IRUV Shade 3 lenses protect against infrared (IR) and ultraviolet radiation (UVA/UVB) during tasks like light cutting and brazing (25692 only)</li> <li>IRUV Shade 5 lenses protect against infrared (IR) and ultraviolet radiation (UVA/UVB) during tasks like medium cutting and brazing (25671 only)</li> </ul>
Base Curve	8.25
Features	<ul style="list-style-type: none"> <li>Sporty, flexible, and lightweight design for comfort and compliance</li> <li>Patented nosepiece design with integrated ridges to divert sweat</li> <li>Every pair includes a neck cord for reduced risk of damage when not being worn</li> <li>Hardcoated lenses for scratch resistance and longer life</li> <li>Anti-Fog coating to prevent fogging; ideal for humid environments and temperature variances (25679, 22476, 22475, 22608, 22610, 22609, 47384, 47387, 47388, 47383, and 47378 only)</li> </ul>
Materials	<ul style="list-style-type: none"> <li>Polycarbonate lens</li> <li>Nylon frame and temple</li> <li>Empilon nose</li> <li>Iron Screws</li> <li>Polyester Neck cord with ABS tightening bead</li> </ul>
Storage	<ul style="list-style-type: none"> <li>Keep in dry, clean conditions away from direct sunlight and chemical and abrasive substances, and protect against mechanical impacts</li> </ul>
Cleaning/Maintenance	<ul style="list-style-type: none"> <li>Rinse thoroughly with warm water and dry with a soft cloth. For anti-fog coated lenses (25679, 22476, 22475, 22608, 22610, 22609, 47384, 47387, 47388, 47383, and 47378) use a soft dry cloth only, as liquids can degrade the performance of the anti-fog coating.</li> <li>Replace eyewear immediately if visibility is reduced or becomes damaged</li> </ul>
Warning:	<ul style="list-style-type: none"> <li>Do not operate a vehicle while wearing IRUV lenses</li> </ul>

For additional information: 1-800-255-6401 or [KCPInfo@kcc.com](mailto:KCPInfo@kcc.com)

Kimberly-Clark warrants that its products (1) comply with K-C's standard specifications as of the delivery date to K-C's authorized distributors/direct purchasers and are warranted for the following periods from end user's date of purchase (verified by valid sales receipt) (a) five years for Balder Technology auto darkening filters; (b) two years for all other auto darkening filters; and (c) one year for powered air purifying respirators; (2) comply with all K-C labeling representations; and (3) are manufactured in compliance with all applicable federal, state, and local laws in effect at the time and place of manufacture of the products. THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. K-C is not liable for any kind of special, incidental, or consequential damages. K-C's liability for breach of contract, tort or other cause of action shall not exceed the product purchase price. Purchasers and users are deemed to have accepted the above warranty and limitation of liability, and cannot change the terms by verbal agreement or by any writing not signed by K-C. To the extent required by applicable law, K-C does not limit its liability for death/injury resulting from K-C's negligence.

®/™Trademarks of Kimberly-Clark Worldwide, Inc. or its affiliates. Marques déposées de Kimberly-Clark Worldwide, Inc. ou de ses filiales. © KCWW.



Revised February 2017